

**16000025**

## ATyS C25ATS Controller

### Strong points

- Flexible space saving
- Cost-effective
- Fast commissioning & testing

### General characteristics

- Self-powered from sensing.
- Voltage supply range (184 - 300 VAC).
- 24 VDC aux power supply (for optional use).
- Main/Main or Main/Genset networks.
- Fixed I/Os.
- RS485 Modbus communication.
- Voltage sensing on all phases.
- Three-phase + Neutral & Single-phase + Neutral networks.
- Phase rotation checking.
- Door or DIN rail mounting.

### Compliance with standards

- IEC 61010-2-201
- IEC 60947-6-1
- GB/T 14048.11 Annex C

### Link to the reference

<https://apac.socomec.com/en/reference/16000025>

ATyS C25 is an entry level ATSE controller with communications. It can be used to pilot a remotely operated transfer switch, such as ATyS r, ATyS S and ATyS d M, as well as contactors. ATyS C25 ensure the automatic or remotely controlled transfer from one source to another with fixed timers and thresholds.

----- System -----	
Fill rate E-Order Common	17
Fill rate E-Order Selection	100
Classification	
UNSPSC	39122331
ETIM Class	EC002498
IGCC	5367
Commerce	
Effective date	2019-01-29
Country of origin	CN
Discount Policy	1CJ80
Discount Policy Label	ATYS RELAY
ETIM - Technical features	
Type of accessory/spare part	Communication and measuring function
Accessory	Yes
Spare part	No
Logistics	
GTIN/EAN	3596033086830
Customs number	8537109199
Price unit	PC
Weight of the packing unit	1.095
Length of the packing unit	0.15
Width of the packing unit	0.125
Depth of the packing unit	0.17
Norms	
Conformity to standards	IEC
Technical Characteristics	
Model	Atys C25