

170H1007

Unipolar fuse base for uR fuses T000-T00 T/80 1000V 400A

Strong points

- High level of electrical safety
- High breaking capacity
- Fuse blown indicator
- Various mounting options

General characteristics

- High level of electrical safety.
- High breaking capacity.
- Fuse blown indicator.
- Various mounting options.

Compliance with standards

- IEC 60269-1
- IEC 60269-2
- IEC 60269-2,-1

Link to the reference

Fuse bases are single-pole or multi-pole solid supports for knife-edge fuses.

Classification

UNSPSC	39121628
ETIM Class	EC000067
IGCC	4982

Commerce

Effective date	1992-05-25
Country of origin	HU

ETIM - Electrical characteristics

Number of poles	1
Rated current [A]	400

ETIM - Mechanical characteristics

Construction size	NH00
-------------------	------

ETIM - Technical features

Bus-mounting type	No
Swivelling mechanism	No

Logistics

GTIN/EAN	3596031020669
Customs number	8536109090
Price unit	PC
Weight of the packing unit	0.3
Length of the packing unit	0.16
Width of the packing unit	0.055
Depth of the packing unit	0.07

Norms

Conformity to standards	IEC
-------------------------	-----

Technical Characteristics

Fuse size	NH000-NH00
Number of poles	1
Rated current	400
Type	I-0

<https://apac.socomec.com/en/reference/170H1007>