

[DC & PV Switch disconnectors](#) - [Load Break Switching \(LBS\)](#) - [Power Protection, Transfer & Distribution](#)

# INOSYS LBS 1000VDC 2P 400A UL

**87P02040**

DC LOAD BREAK SWITCH INOSYS LBS MANUEL UL 400A 2P 1000VDC F3

## Classification

UNSPSC	39122233
ETIM Class	EC000216
IGCC	5290

## Commerce

Discount Policy Label	INOSYS LBS PV MANUAL
Country of origin	FR
Weight	0.01
Length of the product unit	0.2
Width of the product unit	0.137
Depth of the product unit	0.11

### Load break switch

Rated current	400
Number of poles	2
Frame size	F3
Control operator	Direct : E3 / External : S2L
Rated voltage	1000

### Logistics

GTIN/EAN	3596032977702
Customs number	85365080
Price unit	PC
Weight of the packing unit	3.772
Length of the packing unit	0.16
Width of the packing unit	0.39
Depth of the packing unit	0.21

### Norms

Conformity to standards	IEC UL
-------------------------	-----------

### Technical Characteristics

Type	Frontal or lateral operation
------	------------------------------