

[DC & PV Switch disconnectors](#) - [Load Break Switching \(LBS\)](#) - [Power Protection, Transfer & Distribution](#)

INOSYS LBS 1500VDC 1+1 100A UL

87P11011

Classification

UNSPSC	39122233
ETIM Class	EC000216
IGCC	5290

Commerce

Discount Policy Label	INOSYS LBS PV MANUAL
Country of origin	FR

Load break switch

Rated current	100
Number of poles	1+1
Frame size	F2
Control operator	Direct : E2 / External : S2
Rated voltage	1500

Logistics

GTIN/EAN	3596033046735
Customs number	8535301090
Price unit	PC
Weight of the packing unit	0.01

Technical Characteristics

Type	Frontal or lateral operation
------	------------------------------