

[DC & PV Switch disconnectors](#) - [Load Break Switching \(LBS\)](#) - [Power Protection, Transfer & Distribution](#)

# INOSYS LBS 1500VDC 2+2 500A UL

**87P22051**

DC LOAD BREAK SWITCH INOSYS LBS MANUEL UL 2x500A 2+2P 1500VDC F3

## Classification

UNSPSC	39122233
ETIM Class	EC000216
IGCC	5290

## Commerce

Discount Policy Label	INOSYS LBS PV MANUAL
Country of origin	FR

## Load break switch

Rated current	500 (x2)
Number of poles	2+2
Frame size	F3
Control operator	Direct : E3 / External : S2L
Rated voltage	1500

## Logistics

GTIN/EAN	3596033084386
Customs number	85353010
Price unit	PC
Weight of the packing unit	3.6

## Norms

Conformity to standards	CCC IEC UL
-------------------------	------------------

## Technical Characteristics

Type	Frontal or lateral operation
------	------------------------------