

**36256014**

## Switch-discon-fuse FUSERBLOC W/O handle-L R OP-160A-4P-BS-Fuse A3-A4C

### Strong points

- Improved safety
- High breaking capacity
- Multi-use
- Simplified use

### General characteristics

- For industrial fuses up to 1250 A.
- 2P, 3P or 4P available.
- Up to 690 VAC.
- Up to 100 kA.

### Compliance with standards

- IEC 60947-3
- BS EN 60947-3
- IEC 60269-1
- IEC 60269-2

### Link to the reference

<https://apac.socomec.com/en/reference/36256014>

FUSERBLOC BS 88 units with right front-side operation are manually-operated multipole fuse load break switches. They provide make and break on load and safety isolation and protection against overcurrent for any low voltage electrical circuit. This range is available in direct and external operation, in 2, 3 and 4 poles and up to 1250 A.

### ==== System =====

|                             |    |
|-----------------------------|----|
| Fill rate E-Order Common    | 83 |
| Fill rate E-Order Selection | 80 |

### Classification

|            |          |
|------------|----------|
| UNSPSC     | 39122233 |
| ETIM Class | EC001040 |
| IGCC       | 5291     |

### Commerce

|                            |                    |
|----------------------------|--------------------|
| Effective date             | 1998-06-09         |
| Obsolescence date          | 2023-06-30         |
| Production ban date        | 2023-12-30         |
| Country of origin          | FR                 |
| Discount Policy            | 1CC44              |
| Discount Policy Label      | FUSERBLOC MODUL BS |
| Length of the product unit | 0.162              |
| Width of the product unit  | 0.188              |
| Depth of the product unit  | 0.173              |
| Weight                     | 2.62               |

### ETIM - Electrical characteristics

|   |     |
|---|-----|
| Max. rated operation voltage Ue AC [V]          | 690 |
| Rated permanent current Iu [A]                  | 160 |
| Rated operation power at AC-23, 400 V [kW]      | 63  |
| Conditioned rated short-circuit current Iq [kA] | 100 |
| Number of poles                                 | 4   |

### ETIM - Mechanical characteristics

|                                       |            |
|---------------------------------------|------------|
| Cable entry                           | Top/bottom |
| Equipped with connectors              | No         |
| Suitable for floor mounting           | Yes        |
| Suitable for front mounting           | Yes        |
| Suitable for busbar mounting          | No         |
| Degree of protection (IP), front side | IP20       |

### ETIM - Technical features

|   |                 |
|---|-----------------|
| Version as main switch                        | Yes             |
| Version as safety switch                      | Yes             |
| Suitable for fuses                            | Shape A2/A3     |
| With error protection                         | No              |
| Type of electrical connection of main circuit | Bolt connection |
| Type of control element                       | Rocker lever    |
| Position control element                      | Right           |
| Motor drive optional                          | No              |

|  |               |
|--|---------------|
| Motor drive integrated                 | No            |
| Version as emergency stop installation | Yes           |
| <b>Logistics</b>                       |               |
| GTIN/EAN                               | 3596031179756 |
| Customs number                         | 8536309090    |
| Price unit                             | PC            |
| Weight of the packing unit             | 2.62          |
| <b>Norms</b>                           |               |
| Conformity to standards                | IEC           |
| <b>Technical Characteristics</b>       |               |
| Fuse size                              | A3-A4C        |
| Number of poles                        | 4             |
| Rated current                          | 160           |
| Type                                   | I-O           |
| Frame size                             | 3A            |