

49821425



#### Strong points

- Monobloc design
- Plug-in module
- Remote signalling
- End of service life indicator

#### General characteristics

- Type 2 surge arrester.
- 2, 3 or 4 poles
- For distribution boards
- In: 20 kA.
- Imax: 40 kA.
- Common/differential mode.
- Monobloc base.
- Plug-in module.
- Remote signalling.
- End of service life indicator on front

#### Compliance with standards

- NF EN 61643-11
- IEC 61643-11

#### Link to the reference

<https://apac.socomec.com/en/reference/49821425>

The SURGYS D40 surge arrester is designed to protect LV distribution circuits and equipment from transient surges. It acts against the surges of industrial movements and those due to lightning.

<b>Classification</b>	
UNSPSC	39121620
ETIM Class	EC000941
IGCC	4951
<b>Commerce</b>	
Effective date	2009-08-31
Country of origin	CN
<b>Logistics</b>	
GTIN/EAN	3596031972333
Customs number	8535400090
Price unit	PC
Weight of the packing unit	0.979
Length of the packing unit	0.1
Width of the packing unit	0.075
Depth of the packing unit	0.04
<b>Norms</b>	
Conformity to standards	IEC
<b>Technical Characteristics</b>	
Number of poles	2
Protection type	Type 2
Rated voltage	230 VAC
Size	2 Modules