

60120000

Cylindrical fuse without striker gG type 10x38 500Vac 0,5A



Strong points

- High-performance
- Increased reliability
- Improved safety

General characteristics

- High-performance.
- High level of reliability.
- Improved safety.

Compliance with standards

- IEC 60269-1
- IEC 60269-2

Link to the reference

<https://apac.socomec.com/en/reference/60120000>

Industrial fuses protect installations and people from overcurrents for any low voltage electrical circuit.

===== System =====

Fill rate E-Order Common	83
Fill rate E-Order Selection	100

Classification

UNSPSC	39121609
ETIM Class	EC002704
IGCC	4905

Commerce

Effective date	1988-04-15
Country of origin	ES
Discount Policy	1CF10
Discount Policy Label	CYLINDRICAL FUSE
Length of the product unit	0.038
Width of the product unit	0.0103
Weight	0.01

ETIM - Electrical characteristics

Breaking capacity [kA]	120
Power loss at rated current [W]	1.43
Voltage type	AC
Rated current [A]	0.5
Rated voltage [V]	500
Rated operating frequency [Hz]	50..60

ETIM - Mechanical characteristics

Size	10x38 mm
------	----------

ETIM - Technical features

Model	Ceramic fuse
-------	--------------

Logistics

GTIN/EAN	3596031377053
Customs number	8536101090
Price unit	PC
Weight of the packing unit	0.01
Length of the packing unit	0.04
Width of the packing unit	0.01
Depth of the packing unit	0.01

Norms

Conformity to standards	IEC
-------------------------	-----

Technical Characteristics

Fuse melting indicator	without striker
Fuse size	10x38
Rated voltage	500 VAC
Rated current	0,5
Type	gG