


60320002

## Cylindrical fuse without striker gG type 22x58 690Vac 2A



### Strong points

- High-performance
- Increased reliability
- Improved safety

### General characteristics

- High-performance.
- High level of reliability.
- Improved safety.

### Compliance with standards

- IEC 60269-1
- IEC 60269-2

### Link to the reference

<https://apac.socomec.com/en/reference/60320002>

Industrial fuses protect installations and people from overcurrents for any low voltage electrical circuit.

#### ===== System =====

Fill rate E-Order Common	83
Fill rate E-Order Selection	100

#### Classification

UNSPSC	39121609
ETIM Class	EC002704
IGCC	4905

#### Commerce

Effective date	1988-04-15
Obsolescence date	2021-09-01
Production ban date	2022-02-01
Country of origin	ES
Discount Policy	1CF10
Discount Policy Label	CYLINDRICAL FUSE
Length of the product unit	0.058
Width of the product unit	0.0222
Weight	0.05

#### ETIM - Electrical characteristics

Voltage type	AC
Rated current [A]	2
Rated operating frequency [Hz]	50..60

#### ETIM - Mechanical characteristics

Size	14x51 mm
------	----------

#### ETIM - Technical features

Model	Ceramic fuse
-------	--------------

#### Logistics

GTIN/EAN	3596031377756
Customs number	8536101090
Price unit	PC
Weight of the packing unit	0.05
Length of the packing unit	0.021
Width of the packing unit	0.021
Depth of the packing unit	0.057

#### Norms

Conformity to standards	IEC
-------------------------	-----

#### Technical Characteristics

Fuse melting indicator	without striker
Fuse size	22x58
Rated voltage	690 VAC
Rated current	2
Type	gG