

64310005

Fuse base for fuses with or without a striker T4 1P 1250A

Strong points

- High level of electrical safety
- High breaking capacity
- Fuse blown indicator
- Various mounting options

General characteristics

- High level of electrical safety.
- High breaking capacity.
- Fuse blown indicator.
- Various mounting options.

Compliance with standards

- IEC 60269-1
- IEC 60269-2
- IEC 60269-2,-1

Link to the reference

Fuse bases are single-pole or multi-pole solid supports for knife-edge fuses.

----- System -----

Fill rate E-Order Common	29
Fill rate E-Order Selection	75

Classification

UNSPSC	39121624
ETIM Class	EC000067
IGCC	4972

Commerce

Effective date	1988-04-15
Country of origin	FR
Discount Policy	1CF60
Discount Policy Label	FUSE BASE
Weight	2.41

ETIM - Electrical characteristics

Number of poles	1
Rated current [A]	1250

ETIM - Mechanical characteristics

Construction size	NH4
-------------------	-----

ETIM - Technical features

Bus-mounting type	No
Swivelling mechanism	No

Logistics

GTIN/EAN	3596031381661
Customs number	8536109090
Price unit	PC
Weight of the packing unit	2.41
Length of the packing unit	0.34
Width of the packing unit	0.13
Depth of the packing unit	0.075

Norms

Conformity to standards	IEC
-------------------------	-----

Technical Characteristics

Fuse size	NH4
Number of poles	1
Rated current	1250

<https://apac.socomec.com/en/reference/64310005>