

**65001010**

## Fuse base for fuses without a striker T00 1P 160A back plate mounted device



### Strong points

- High level of electrical safety
- High breaking capacity
- Fuse blown indicator
- Various mounting options

### General characteristics

- High level of electrical safety.
- High breaking capacity.
- Fuse blown indicator.
- Various mounting options.

### Compliance with standards

- IEC 60269-1
- IEC 60269-2
- IEC 60269-2,-1

### Link to the reference

<https://apac.socomec.com/en/reference/65001010>

Fuse bases are single-pole or multi-pole solid supports for knife-edge fuses.

----- System -----	
Fill rate E-Order Common	43
Fill rate E-Order Selection	75
Classification	
UNSPSC	39121624
ETIM Class	EC000067
IGCC	4972
Commerce	
Effective date	2003-01-09
Country of origin	ES
Discount Policy	1CF60
Discount Policy Label	FUSE BASE
Weight	0.12
ETIM - Electrical characteristics	
Number of poles	1
Rated current [A]	160
ETIM - Mechanical characteristics	
Construction size	NH00
ETIM - Technical features	
Bus-mounting type	No
Swivelling mechanism	No
Logistics	
GTIN/EAN	3596031652266
Customs number	8536109090
Price unit	PC
Weight of the packing unit	0.12
Length of the packing unit	0.125
Width of the packing unit	0.04
Depth of the packing unit	0.06
Norms	
Conformity to standards	IEC
Technical Characteristics	
Fuse size	NH00
Number of poles	1
Rated current	160
Type	Screw mounting