

66000050

Knife-edge fuse without striker gG type NH S000/00C 500Vac 50A



Strong points

- High-performance
- Increased reliability
- Improved safety

General characteristics

- High-performance.
- High level of reliability.
- Improved safety.

Compliance with standards

- IEC 60269-1
- IEC 60269-2

Link to the reference

<https://apac.socomec.com/en/reference/66000050>

Industrial fuses protect installations and people from overcurrents for any low voltage electrical circuit.

===== System =====

Fill rate E-Order Common	100
Fill rate E-Order Selection	100

Classification

UNSPSC	39121612
ETIM Class	EC000055
IGCC	4908

Commerce

Effective date	1990-10-31
Country of origin	HU
Discount Policy	1CF20
Discount Policy Label	FUSE WITHOUT STRIKER
Length of the product unit	0.048
Width of the product unit	0.08
Depth of the product unit	0.03
Weight	0.122

ETIM - Electrical characteristics

Voltage type	AC
Rated current [A]	50
Rated voltage AC [V]	500

ETIM - Mechanical characteristics

Type of fuse status indicator	None
-------------------------------	------

ETIM - Technical features

Fuse construction type according to IEC 60269	NHC00
---	-------

Logistics

GTIN/EAN	3596031383689
Customs number	8536105090
Price unit	PC
Weight of the packing unit	0.122
Length of the packing unit	0.08
Width of the packing unit	0.055
Depth of the packing unit	0.02

Norms

Conformity to standards	IEC
-------------------------	-----

Technical Characteristics

Fuse melting indicator	without striker
Fuse size	S000/00C
Rated voltage	500 VAC
Rated current	50
Type	gG