

66920125

Knife-edge fuse without striker gG type NH S00 500Vac 125A



Strong points

- High-performance
- Increased reliability
- Improved safety

General characteristics

- High-performance.
- High level of reliability.
- Improved safety.

Compliance with standards

- IEC 60269-1
- IEC 60269-2

Link to the reference

<https://apac.socomec.com/en/reference/66920125>

Industrial fuses protect installations and people from overcurrents for any low voltage electrical circuit.

Classification	
UNSPSC	39121612
ETIM Class	EC000055
IGCC	4908
Commerce	
Effective date	1988-04-15
Country of origin	HU
Length of the product unit	0.048
Width of the product unit	0.08
Depth of the product unit	0.03
Weight	0.19
ETIM - Electrical characteristics	
Voltage type	AC
Rated current [A]	125
Rated voltage AC [V]	500
ETIM - Mechanical characteristics	
Type of fuse status indicator	None
ETIM - Technical features	
Fuse construction type according to IEC 60269	NH00
Logistics	
GTIN/EAN	3596031384914
Customs number	8536109090
Price unit	PC
Weight of the packing unit	0.19
Length of the packing unit	0.08
Width of the packing unit	0.06
Depth of the packing unit	0.032
Norms	
Conformity to standards	IEC
Technical Characteristics	
Fuse melting indicator	without striker
Fuse size	S00
Rated voltage	500 VAC
Rated current	125
Type	gG