

67030040

Knife-edge fuse without striker aM type NH S0 500Vac 40A



Strong points

- High-performance
- Increased reliability
- Improved safety

General characteristics

- High-performance.
- High level of reliability.
- Improved safety.

Compliance with standards

- IEC 60269-1
- IEC 60269-2

Link to the reference

<https://apac.socomec.com/en/reference/67030040>

Socomec industrial fuses protect installations and people from overcurrents for low voltage electrical circuits.

Classification	
UNSPSC	39121612
ETIM Class	EC000055
IGCC	4908
Commerce	
Effective date	1988-04-15
Obsolescence date	2021-09-01
Production ban date	2022-02-01
Country of origin	HU
Length of the product unit	0.048
Width of the product unit	0.1275
Depth of the product unit	0.04
Weight	0.25
ETIM - Electrical characteristics	
Voltage type	AC
Rated current [A]	40
Rated voltage AC [V]	500
Utilization category	aM (switchgear protection)
ETIM - Mechanical characteristics	
Type of fuse status indicator	None
ETIM - Technical features	
Fuse construction type according to IEC 60269	NH0
Logistics	
GTIN/EAN	3596031385355
Customs number	8536105090
Price unit	PC
Weight of the packing unit	0.26
Length of the packing unit	0.13
Width of the packing unit	0.05
Depth of the packing unit	0.034
Norms	
Conformity to standards	IEC
Technical Characteristics	
Fuse melting indicator	without striker
Fuse size	S0
Rated voltage	500 VAC
Rated current	40
Type	aM