

67120125

Knife-edge fuse without striker gG type NH S1 500Vac 125A



Strong points

- High-performance
- Increased reliability
- Improved safety

General characteristics

- High-performance.
- High level of reliability.
- Improved safety.

Compliance with standards

- IEC 60269-1
- IEC 60269-2

Link to the reference

<https://apac.socomec.com/en/reference/67120125>

Industrial fuses protect installations and people from overcurrents for any low voltage electrical circuit.

===== System =====

Fill rate E-Order Common	100
Fill rate E-Order Selection	100

Classification

UNSPSC	39121612
ETIM Class	EC000055
IGCC	4908

Commerce

Effective date	1988-04-15
Country of origin	HU
Discount Policy	1CF20
Discount Policy Label	FUSE WITHOUT STRIKER
Length of the product unit	0.053
Width of the product unit	0.1375
Depth of the product unit	0.052
Weight	0.393

ETIM - Electrical characteristics

Voltage type	AC
Rated current [A]	125
Rated voltage AC [V]	500

ETIM - Mechanical characteristics

Type of fuse status indicator	None
-------------------------------	------

ETIM - Technical features

Fuse construction type according to IEC 60269	NH1
---	-----

Logistics

GTIN/EAN	3596031386796
Customs number	8536109090
Price unit	PC
Weight of the packing unit	0.393
Length of the packing unit	0.028
Width of the packing unit	0.057
Depth of the packing unit	0.072

Norms

Conformity to standards	IEC
-------------------------	-----

Technical Characteristics

Fuse melting indicator	without striker
Fuse size	S1
Rated voltage	500 VAC
Rated current	125
Type	gG