

67130100

Knife-edge fuse without striker aM type NH S1 500Vac 100A



Strong points

- High-performance
- Increased reliability
- Improved safety

General characteristics

- High-performance.
- High level of reliability.
- Improved safety.

Compliance with standards

- IEC 60269-1
- IEC 60269-2

Link to the reference

<https://apac.socomec.com/en/reference/67130100>

Socomec industrial fuses protect installations and people from overcurrents for low voltage electrical circuits.

===== System =====	
Fill rate E-Order Common	100
Fill rate E-Order Selection	100
Classification	
UNSPSC	39121612
ETIM Class	EC000055
IGCC	4908
Commerce	
Effective date	1988-04-15
Country of origin	HU
Discount Policy	1CF20
Discount Policy Label	FUSE WITHOUT STRIKER
Length of the product unit	0.053
Width of the product unit	0.1375
Depth of the product unit	0.052
Weight	0.395
ETIM - Electrical characteristics	
Voltage type	AC
Rated current [A]	100
Rated voltage AC [V]	500
Utilization category	aM (switchgear protection)
ETIM - Mechanical characteristics	
Type of fuse status indicator	None
ETIM - Technical features	
Fuse construction type according to IEC 60269	NH1
Logistics	
GTIN/EAN	3596031387816
Customs number	8536109090
Price unit	PC
Weight of the packing unit	0.395
Length of the packing unit	0.07
Width of the packing unit	0.13
Depth of the packing unit	0.14
Norms	
Conformity to standards	IEC
Technical Characteristics	
Fuse melting indicator	without striker
Fuse size	S1
Rated voltage	500 VAC
Rated current	100
Type	gG