

67461000

Knife-edge fuse without striker gG type NH S4 500Vac 1000A



Strong points

- High-performance
- Increased reliability
- Improved safety

General characteristics

- High-performance.
- High level of reliability.
- Improved safety.

Compliance with standards

- IEC 60269-1
- IEC 60269-2

Link to the reference

<https://apac.socomec.com/en/reference/67461000>

Industrial fuses protect installations and people from overcurrents for any low voltage electrical circuit.

Classification	
UNSPSC	39121612
ETIM Class	EC000055
IGCC	4908
Commerce	
Effective date	1988-04-15
Country of origin	ES
Length of the product unit	0.11
Width of the product unit	0.203
Depth of the product unit	0.105
Weight	2.19
ETIM - Electrical characteristics	
Voltage type	AC
Rated current [A]	1000
Rated voltage AC [V]	500
ETIM - Mechanical characteristics	
Type of fuse status indicator	None
ETIM - Technical features	
Fuse construction type according to IEC 60269	NH4
Logistics	
GTIN/EAN	3596031396047
Customs number	8536109090
Price unit	PC
Weight of the packing unit	2.19
Length of the packing unit	0.225
Width of the packing unit	0.135
Depth of the packing unit	0.115
Norms	
Conformity to standards	IEC
Technical Characteristics	
Fuse melting indicator	without striker
Fuse size	S4
Rated voltage	500 VAC
Rated current	1000
Type	gG