

**68530032**

## Knife-edge fuse with striker aM type NH S0 690Vac 32A



### Strong points

- High-performance
- Increased reliability
- Improved safety

### General characteristics

- High-performance.
- High level of reliability.
- Improved safety.

### Compliance with standards

- IEC 60269-1
- IEC 60269-2

### Link to the reference

<https://apac.socomec.com/en/reference/68530032>

Socomec industrial fuses protect installations and people from overcurrents for low voltage electrical circuits.

===== System =====	
Fill rate E-Order Common	100
Fill rate E-Order Selection	100
Classification	
UNSPSC	39121612
ETIM Class	EC000055
IGCC	4908
Commerce	
Effective date	1988-04-15
Obsolescence date	2021-09-01
Production ban date	2022-02-01
Country of origin	ES
Discount Policy	1CF30
Discount Policy Label	FUSE WITH STRIKER
Length of the product unit	0.048
Width of the product unit	0.1275
Depth of the product unit	0.045
Weight	0.29
ETIM - Electrical characteristics	
Voltage type	AC
Rated current [A]	32
Rated voltage AC [V]	690
Utilization category	aM (switchgear protection)
ETIM - Technical features	
Fuse construction type according to IEC 60269	NH0
Logistics	
GTIN/EAN	3596031408153
Customs number	8536105090
Price unit	PC
Weight of the packing unit	0.29
Length of the packing unit	0.04
Width of the packing unit	0.045
Depth of the packing unit	0.123
Norms	
Conformity to standards	IEC
Technical Characteristics	
Fuse melting indicator	with striker
Fuse size	S0
Rated voltage	690 VAC
Rated current	32
Type	aM