

68530040

Knife-edge fuse with striker aM type NH S0 690Vac 40A



Strong points

- High-performance
- Increased reliability
- Improved safety

General characteristics

- High-performance.
- High level of reliability.
- Improved safety.

Compliance with standards

- IEC 60269-1
- IEC 60269-2

Link to the reference

<https://apac.socomec.com/en/reference/68530040>

Socomec industrial fuses protect installations and people from overcurrents for low voltage electrical circuits.

----- System -----

Fill rate E-Order Common	100
Fill rate E-Order Selection	100

Classification

UNSPSC	39121612
ETIM Class	EC000055
IGCC	4908

Commerce

Effective date	1988-04-15
Obsolescence date	2021-09-01
Production ban date	2022-02-01
Country of origin	ES
Discount Policy	1CF30
Discount Policy Label	FUSE WITH STRIKER
Length of the product unit	0.048
Width of the product unit	0.1275
Depth of the product unit	0.045
Weight	0.296

ETIM - Electrical characteristics

Voltage type	AC
Rated current [A]	40
Rated voltage AC [V]	690
Utilization category	aM (switchgear protection)

ETIM - Technical features

Fuse construction type according to IEC 60269	NH0
---	-----

Logistics

GTIN/EAN	3596031408160
Customs number	8536105090
Price unit	PC
Weight of the packing unit	0.296
Length of the packing unit	0.055
Width of the packing unit	0.04
Depth of the packing unit	0.12

Norms

Conformity to standards	IEC
-------------------------	-----

Technical Characteristics

Fuse melting indicator	with striker
Fuse size	S0
Rated voltage	690 VAC
Rated current	40
Type	aM