

**68530080**

## Knife-edge fuse with striker aM type NH S0 690Vac 80A



### Strong points

- High-performance
- Increased reliability
- Improved safety

### General characteristics

- High-performance.
- High level of reliability.
- Improved safety.

### Compliance with standards

- IEC 60269-1
- IEC 60269-2

### Link to the reference

<https://apac.socomec.com/en/reference/68530080>

Socomec industrial fuses protect installations and people from overcurrents for low voltage electrical circuits.

<b>Classification</b>	
UNSPSC	39121612
ETIM Class	EC000055
IGCC	4908
<b>Commerce</b>	
Effective date	1988-04-15
Country of origin	ES
Length of the product unit	0.048
Width of the product unit	0.1275
Depth of the product unit	0.045
Weight	0.29
<b>ETIM - Electrical characteristics</b>	
Voltage type	AC
Rated current [A]	80
Rated voltage AC [V]	690
Utilization category	aM (switchgear protection)
<b>ETIM - Technical features</b>	
Fuse construction type according to IEC 60269	NH0
<b>Logistics</b>	
GTIN/EAN	3596031408191
Customs number	8536109090
Price unit	PC
Weight of the packing unit	0.29
Length of the packing unit	0.125
Width of the packing unit	0.06
Depth of the packing unit	0.04
<b>Norms</b>	
Conformity to standards	IEC
<b>Technical Characteristics</b>	
Fuse melting indicator	with striker
Fuse size	S0
Rated voltage	690 VAC
Rated current	80
Type	aM