

**68960500**

## Knife-edge fuse with striker gG type NH S4 500Vac 500A



### Strong points

- High-performance
- Increased reliability
- Improved safety

### General characteristics

- High-performance.
- High level of reliability.
- Improved safety.

### Compliance with standards

- IEC 60269-1
- IEC 60269-2

### Link to the reference

<https://apac.socomec.com/en/reference/68960500>

Industrial fuses protect installations and people from overcurrents for any low voltage electrical circuit.

<b>Classification</b>	
UNSPSC	39121612
ETIM Class	EC000055
IGCC	4908
<b>Commerce</b>	
Effective date	1988-04-15
Obsolescence date	2021-09-01
Production ban date	2022-02-01
Country of origin	ES
Length of the product unit	0.11
Width of the product unit	0.203
Depth of the product unit	0.105
Weight	2.207
<b>ETIM - Electrical characteristics</b>	
Voltage type	AC
Rated current [A]	500
Rated voltage AC [V]	500
<b>ETIM - Technical features</b>	
Fuse construction type according to IEC 60269	NH4
<b>Logistics</b>	
GTIN/EAN	3596031408818
Customs number	8536109090
Price unit	PC
Weight of the packing unit	2.227
Length of the packing unit	0.135
Width of the packing unit	0.115
Depth of the packing unit	0.22
<b>Norms</b>	
Conformity to standards	IEC
<b>Technical Characteristics</b>	
Fuse melting indicator	with striker
Fuse size	S4
Rated voltage	500 VAC
Rated current	500
Type	gG