

68961200

Knife-edge fuse with striker gG type NH S4 500Vac 1250A



Strong points

- High-performance
- Increased reliability
- Improved safety

General characteristics

- High-performance.
- High level of reliability.
- Improved safety.

Compliance with standards

- IEC 60269-1
- IEC 60269-2

Link to the reference

<https://apac.socomec.com/en/reference/68961200>

Industrial fuses protect installations and people from overcurrents for any low voltage electrical circuit.

===== System =====

Fill rate E-Order Common	100
Fill rate E-Order Selection	100

Classification

UNSPSC	39121612
ETIM Class	EC000055
IGCC	4908

Commerce

Effective date	1988-04-15
Country of origin	ES
Discount Policy	1CF30
Discount Policy Label	FUSE WITH STRIKER
Length of the product unit	0.11
Width of the product unit	0.203
Depth of the product unit	0.105
Weight	2.468

ETIM - Electrical characteristics

Voltage type	AC
Rated current [A]	1250
Rated voltage AC [V]	500

ETIM - Technical features

Fuse construction type according to IEC 60269	NH4
---	-----

Logistics

GTIN/EAN	3596031408870
Customs number	8536109090
Price unit	PC
Weight of the packing unit	2.468
Length of the packing unit	0.114
Width of the packing unit	0.135
Depth of the packing unit	0.224

Norms

Conformity to standards	IEC
-------------------------	-----

Technical Characteristics

Fuse melting indicator	with striker
Fuse size	S4
Rated voltage	500 VAC
Rated current	1250
Type	gG