

NPE-0850

NETYS PE 850VA USB



Strong points

- Ideal and cost-effective protection for SOHO or POS applications
- Easy to use
- A solution for network power cuts and voltage fluctuations
- Simplified connection
- Protection for your data line

General characteristics

- Minitower case.
- Step Wave, AVR function (Automatic Voltage Regulation).
- Control panel with LCD display.
- LOCAL VIEW software for local UPS monitoring.
- NTP data line suppressor.
- Up to 6 UPS output sockets.

Compliance with standards

- IEC/EN 62040-1, IEC/EN 62040-2
- AS 62040.1.1, AS 62040.1.2, AS 62040.2
- CE
- RCM (E2376)

Link to the reference

<https://apac.socomec.com/en/reference/NPE-0850>

Protection for small office, personal or point-of-sale applications.

Classification

UNSPSC	39121011
ETIM Class	EC000382
IGCC	4149

Commerce

Description (240 char.)	NeTYS PE 850VA/480W 230V 50/60Hz BATTERY INCLUDED WITH AVR, STEPWAVE PLUGS PROTECTED RJ45, 1xUSB
Effective date	2012-09-01
Country of origin	CN
Discount Policy	D02
Discount Policy Label	NETYS PE
Length of the product unit	0.145
Width of the product unit	0.1
Depth of the product unit	0.3
Weight	6

ETIM - Electrical characteristics

Input voltage [V]	140..300
Primary frequency [Hz]	45..66
Number of phases primary	1
Output voltage [V]	230..230
Secondary frequency [Hz]	50..60
Output effective power [W]	480
Output apparent power [VA]	850
Number of phases secondary	1
SNMP	Yes
Voltage type	AC
Output power factor	0.6

ETIM - Mechanical characteristics

Height [mm]	145
Width [mm]	100
Depth [mm]	300
Weight [kg]	6
Construction type	Free standing model
Input connection	C14
Number of output connections C13	4

ETIM - Technical features

USB interface	Yes
Bridging time full load [min]	3
Suitable for network-management	Yes
USV- technology	Line-interactive
Overall efficiency [%]	98
Efficiency in eco-mode [%]	98
Potential free switch contact	Yes
Auto shut down function	Yes

Logistics

GTIN/EAN	8027122515160
Customs number	8504409590
Weight of the packing unit	6
Length of the packing unit	0.3
Width of the packing unit	0.1
Depth of the packing unit	0.145
Technical Characteristics	
Depth	300
Height	145
In/out	1/1
Output voltage	230
Rated frequency	50/50
Width	100
Sn	0.85
Pn	0.48
Conf	M2
Input voltage	230
Rate (min)	0.85
Rate (max)	0.85
Life Time	03-05
Configuration	Line-Interactive UPS with AVR