

NRT2-U3300

NETYS RT 3K3VA 230VAC+BAT



Strong points

- Simple to install
- High protection and availability
- Certified performance
- Easy to use
- Extended and flexible back-up time

General characteristics

- Rail kit.
- Embedded dry-contact interface (5000-11000 VA).
- Input mains switch breaker (5000-11000 VA).
- Connection for battery extension modules.
- Port for parallel operation (5000-11000 VA).
- Power off the UPS remotely.
- Internal temperature sensor.

Compliance with standards

- IEC 62040-1
- IEC 62040-2
- IEC 62040-3
- AS 62040.1.1
- AS 62040.1.2
- AS 62040.2
- RCM (E2376)

Link to the reference

<https://apac.socomec.com/en/reference/NRT2-U3300>

Complete and professional, NETYS RT is a single-phase rack-tower UPS ensuring protection and availability of IT infrastructure that meet both requirements of power reliability and installation flexibility.

Classification	
UNSPSC	39121011
ETIM Class	EC000382
IGCC	4149
Commerce	
Description (240 char.)	NeTYS RT 3300VA/2700W VFI UPS 1/1 WITH BATTERY INTEGRATED +RAILS
Effective date	2016-04-30
Country of origin	CN
Discount Policy	D04
Discount Policy Label	NETYS RT
Length of the product unit	0.089
Width of the product unit	0.44
Depth of the product unit	0.608
Weight	30
ETIM - Electrical characteristics	
Input voltage [V]	175..280
Primary frequency [Hz]	45..66
Number of phases primary	1
Output voltage [V]	200..240
Secondary frequency [Hz]	50..60
Output effective power [W]	2700
Output apparent power [VA]	3300
Number of phases secondary	1
SNMP	Yes
Voltage type	AC
Max. voltage distortion output (linear load) [%]	2
Output power factor	0.82
ETIM - Mechanical characteristics	
Height [mm]	440
Width [mm]	88.7
Depth [mm]	608
Weight [kg]	30
Construction type	482.6 mm (19 inch) device
Input connection	C20
Number of output connections C13	6
Number of output connections C19	1
ETIM - Technical features	
USB interface	No
Bridging time full load [min]	6.8
Suitable for network-management	Yes
USV- technology	Online
Overall efficiency [%]	93
Efficiency in eco-mode [%]	98
Potential free switch contact	Yes

Auto shut down function	Yes
Logistics	
GTIN/EAN	8027122601146
Customs number	8504409590
Weight of the packing unit	30
Length of the packing unit	0.608
Width of the packing unit	0.44
Depth of the packing unit	0.089
Norms	
Conformity to standards	IEC
Technical Characteristics	
Depth	608
Height	89
In/out	1/1
Output voltage	230
Rated frequency	50/50
Width	440
Sn	3.3
Pn	2.7
Conf	C1
Input voltage	230
Rate (min)	3.3
Rate (max)	3.3
Life Time	03-05
Typical Backup Time	7
Configuration	UPS Single Unit(s) with Bypass