

**Manufacturer** SOCOMECSAS  
1-4 rue de Westhouse  
67230 BENFELD  
FRANCE

**Product type** **Transfer switching equipment fitted with their original accessories**

**Product model(s)** **ATyS S, ATyS dS, ATyS r, ATyS d, ATyS t, ATyS g, ATyS p**

**Product references** **See next pages**

This declaration of conformity is issued under the sole responsibility of the manufacturer. The above mentioned equipment(s), with respect to the relevant installation, maintenance and use requirements regarding to its (their) destination, regulations, standards and manufacturer instructions, is in conformity with the relevant statutory requirements applicable to the specific product:

**2012 No.3032** ***The Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment Regulations***

**2016 No.1101** ***The Electrical Equipment (Safety) Regulations***

**2016 No.1091** ***The Electromagnetic Compatibility Regulations***

As amended by:  
**2019 No. 696** ***The Product Safety and Metrology etc. (Amendment etc.) (EU Exit) Regulations***

References of designated standards applied:

**2012 No.3032** **EN IEC 63000: 2018**

**2016 No.1101** **EN 60947-6-1:2005/A1:2014**

**2016 No.1091** **EN 60947-6-1:2005/A1:2014**

This declaration shall cease to be valid if any modification is made on the equipment(s).

**Date** **7/24/2023**

**Place** **Benfeld**



**Alan REED**  
*Power Switching & Monitoring Application Director*



Product models	Voltage tap	Bridging Bar	Terminal shroud	Other accessories
<b>ATyS S</b> 95054004 ; 95064004 ; 95054006 ; 95064006 ; 95054008 ; 95064008 ; 95054010 ; 95064010 ; 95054012 ; 95064012				<b>Autotransformer</b> 95994004
95034004 ; 95034006 ; 95034008 ; 95034010 ; 95034012	95994001	95034013	<b>Line side</b> 95944012  <b>Load side</b> 95949012	<b>Terminal retainer</b> 95994003  <b>DIN rail</b> 95994002
<b>ATyS dS</b> 95134004 ; 95134006 ; 95134008 ; 95134010 ; 95134012				

Product models	Bridging Bar	Terminal screen	Lug kit	Auxiliary contact
<b>ATyS UL</b> 97232010 ; 97233010 ; 97234010 ; 97232020 97233020 ; 97234020	41592021 41593021 41594021	41583021 41584021	39542020 39543020 39544020	41590021 41590022
97232026 ; 97233026 ; 97234026 ; 97232040 97233040 ; 97234040	41592041 41593041 41594041	41583041 41584041	39542040 39543040 39544040	

Product models ATyS r	Bridging Bar	Terminal shroud	Terminal screen	Solid neutral	Auxiliary contact	2-position padlocking	Key handle interlocking system	Mounting spacer	Door protective surround	Other accessories	Copper bar connection kit
95233012 ; 95234012 95233016 ; 95234016 95233020 ; 95234020	41093019 41094019	26943014 26944014	15093012 15094012	95090012							
95233025 ; 95234025	41093025 41094025										
95233031 ; 95234031	41093039 41094039	26943021 26944021	15093025 15094025	95090025	15990502	95990003	95991006	15090001	15290012		
95233040 ; 95234040				95090040							
95233050 ; 95234050	41093050 41094050										
95233063 ; 95234063	41093063 41094063	26943051 26944051	15093063 15094063	95090063							
95233080 ; 95234080	41093080 41094080										
95233100 ; 95234100			15093080 15094080	95090080							
95233120 ; 95234120	41093120 41094120			95090120	15990532						
95233160 ; 95234160	41093160 41094160		15093160 15094160	95090160		95990004	95991004		15290080		
95233200 ; 95234200											
95233250 ; 95234250			15093200 15094200		<b>Included d'origine</b>						26191200 26291200 26991200 41090320
95233320 ; 95234320											26291200 26991200 41090320

Product models ATyS d	Bridging Bar	Terminal shroud	Terminal screen	Solid neutral	Auxiliary contact	2-position padlocking	Key handle interlocking system	Mounting spacer	Door protective surround	Other accessories	Copper bar connection kit
95333012 ; 95334012 95333016 ; 95334016 95333020 ; 95334020	41093019 41094019	26943014 26944014	15093012 15094012	95090012	15990502	95990003	95991006	15090001	15390012	<b>Autotransformer</b> 15994064  <b>DC power supply</b> 15995012 15995112 15995212  <b>Double power supply</b> 15994001  <b>Remote Interface</b> 95992010  <b>Connecting cable for remote interface</b> 15992009	
95333025 ; 95334025	41093025 41094025	26943021 26944021	15093025 15094025	95090025							
95333031 ; 95334031	41093039 41094039		95090040								
95333040 ; 95334040											
95333050 ; 95334050	41093050 41094050	26943051 26944051	15093063 15094063	95090063							
95333063 ; 95334063	41093063 41094063										
95333080 ; 95334080	41093080 41094080		15093080 15094080	95090080	15990532	95990004	95991004	15390080			
95333100 ; 95334100				95090120							
95333120 ; 95334120	41093120 41094120		15093160 15094160	95090160							
95333160 ; 95334160	41093160 41094160										
95333200 ; 95334200			15093200 15094200		Included <i>d'origine</i>						26191200 26291200 26991200 41090320
95333250 ; 95334250											26291200 26991200 41090320
95333320 ; 95334320											

Product models ATyS t	Bridging Bar	Terminal shroud	Terminal screen	Solid neutral	Voltage tapping and power supply kit	Auxiliary contact	2-position padlocking	Key handle interlocking system	Mounting spacer	Door protective surround	Other accessories	Copper bar connection kit	
95433012 ; 95434012 95433016 ; 95434016 95433020 ; 95434020	41093019 41094019	26943014 26944014	15093012 15094012	95090012	15593012 15594012	15990502	95990003	95991006	15090001	15390012	<b>Autotransformer</b> 15994064  <b>DC power supply</b> 15995012 15995112 15995212  <b>Double power supply</b> 15994001  <b>Remote Interface</b> 95992010  <b>Connecting cable for remote interface</b> 15992009		
95433025 ; 95434025	41093025 41094025	26943021 26944021	15093025 15094025	95090025	15593025 15594025								
95433031 ; 95434031 95433040 ; 95434040	41093039 41094039		26943051 26944051	15093063 15094063	95090063								15593063 15594063
95433050 ; 95434050	41093050 41094050	15093063 15094063		95090063	15593063 15594063								
95433063 ; 95434063	41093063 41094063												
95433080 ; 95434080 95433100 ; 95434100	41093080 41094080		15093080 15094080	95090080	15593080 15594080	15990532				15390080	<b>Sealable cover</b> 95990000	26191200 26291200 26991200 41090320  26291200 26991200 41090320	
95433120 ; 95434120	41093120 41094120			15093160 15094160	95090120								15593120 15594120
95433160 ; 95434160	41093160 41094160			15093160 15094160	95090160								15593160 15594160
95433200 ; 95434200							95990004	95991004					
95433250 ; 95434250				15093200 15094200		15593200 15594200							Included <i>d'origine</i>
95433320 ; 95434320													

Product models ATyS g	Bridging Bar	Terminal shroud	Terminal screen	Solid neutral	Voltage tapping and power supply kit	Auxiliary contact	2-position padlocking	Key handle interlocking system	Mounting spacer	Door protective surround	Other accessories	Copper bar connection kit
95533012 ; 95534012 95533016 ; 95534016 95533020 ; 95534020	41093019 41094019	26943014 26944014	15093012 15094012	95090012	15593012 15594012							
95533025 ; 95534025	41093025 41094025	26943021 26944021	15093025 15094025	95090025	15593025 15594025	15990502	95990003	95991006	15090001	15390012	<b>Autotransformer</b> 15994064  <b>DC power supply</b> 15995012 15995112 15995212  <b>Double power supply</b> 15994001	
95533031 ; 95534031	41093039 41094039				15593040 15594040							
95533040 ; 95534040					95090040							
95533050 ; 95534050	41093050 41094050	26943051 26944051	15093063 15094063	95090063	15593063 15594063					<b>Remote Interface</b> 95992010  <b>Connecting cable for remote interface</b> 15992009  <b>Sealable cover</b> 95990000		
95533063 ; 95534063	41093063 41094063											
95533080 ; 95534080	41093080 41094080		15093080 15094080	95090080	15593080 15594080	15990532				15390080		
95533100 ; 95534100												
95533120 ; 95534120	41093120 41094120			95090120	15593120 15594120							
95533160 ; 95534160	41093160 41094160		15093160 15094160	95090160	15593160 15594160	95990004	95991004					
95533200 ; 95534200												
95533250 ; 95534250			15093200 15094200		15593200 15594200					Included <i>d'origine</i>		
95533320 ; 95534320												

Product model ATyS p	Bridging Bar	Terminal shroud	Terminal screen	Solid neutral	Voltage tapping and power supply kit	Auxiliary contact	2-position padlocking	Key handle interlocking system	Mounting spacer	Door protective surround	Other accessories	Copper bar connection kit
95733012 ; 95734012 95733016 ; 95734016 95733020 ; 95734020	41093019 41094019	26943014 26944014	15093012 15094012	95090012	15593012 15594012	15990502	95990003	95991006	15090001	15390012	<b>Autotransformer</b>  15994064  <b>DC power supply</b> 15995012 15995112 15995212  <b>Double power supply</b> 15994001  <b>Remote Interface</b> 95992020  <b>Connecting cable for remote interface</b> 15992009	
95733025 ; 95734025	41093025 41094025	26943021 26944021	15093025 15094025	95090025	15593025 15594025							
95733031 ; 95734031 95733040 ; 95734040	41093039 41094039		26943051 26944051	15093063 15094063	95090040							
95733050 ; 95734050	41093050 41094050	95090063			15593063 15594063							
95733063 ; 95734063	41093063 41094063											
95733080 ; 95734080 95733100 ; 95734100	41093080 41094080		15093080 15094080	95090080	15593080 15594080	15990532				15390080	<b>Remote Interface</b> 95992020  <b>Connecting cable for remote interface</b> 15992009	
95733120 ; 95734120	41093120 41094120			95090120	15593120 15594120							
95733160 ; 95734160	41093160 41094160		15093160 15094160	95090160	15593160 15594160	95990004	95991004					
95733200 ; 95734200												
95733250 ; 95734250			15093200 15094200		15593200 15594200	<b>Included</b>					26191200 26291200 26991200 41090320	
95733320 ; 95734320											26291200 26991200 41090320	