

67030020

## Knife-edge fuse without striker aM type NH S0 500Vac 20A



### Strong points

- High-performance
- Increased reliability
- Improved safety

### General characteristics

- High-performance.
- High level of reliability.
- Improved safety.

### Compliance with standards

- IEC 60269-1
- IEC 60269-2

### Link to the reference

<https://apac.socomec.com/en/reference/67030020>

Socomec industrial fuses protect installations and people from overcurrents for low voltage electrical circuits.

|   |                            |
|---|----------------------------|
| <b>----- System -----</b>                     |                            |
| Fill rate E-Order Common                      | 100                        |
| Fill rate E-Order Selection                   | 100                        |
| <b>Classification</b>                         |                            |
| UNSPSC  | 39121612                   |
| ETIM Class                                    | EC000055                   |
| IGCC  | 4908                       |
| <b>Commerce</b>                               |                            |
| Effective date                                | 1988-04-15                 |
| Obsolescence date                             | 2021-09-01                 |
| Production ban date                           | 2022-02-01                 |
| Country of origin                             | HU                         |
| Discount Policy                               | 1CF20                      |
| Discount Policy Label                         | FUSE WITHOUT STRIKER       |
| Length of the product unit                    | 0.048                      |
| Width of the product unit                     | 0.1275                     |
| Depth of the product unit                     | 0.04                       |
| Weight  | 0.254                      |
| <b>ETIM - Electrical characteristics</b>      |                            |
| Voltage type                                  | AC                         |
| Rated current [A]                             | 20                         |
| Rated voltage AC [V]                          | 500                        |
| Utilization category                          | aM (switchgear protection) |
| <b>ETIM - Mechanical characteristics</b>      |                            |
| Type of fuse status indicator                 | None                       |
| <b>ETIM - Technical features</b>              |                            |
| Fuse construction type according to IEC 60269 | NH0                        |
| <b>Logistics</b>                              |                            |
| GTIN/EAN                                      | 3596031385324              |
| Customs number                                | 8536105090                 |
| Price unit                                    | PC                         |
| Weight of the packing unit                    | 0.254                      |
| Length of the packing unit                    | 0.07                       |
| Width of the packing unit                     | 0.1                        |
| Depth of the packing unit                     | 0.13                       |
| <b>Norms</b>                                  |                            |
| Conformity to standards                       | IEC                        |
| <b>Technical Characteristics</b>              |                            |
| Fuse melting indicator                        | without striker            |
| Fuse size                                     | S0                         |
| Rated voltage                                 | 500 VAC                    |
| Rated current                                 | 20                         |
| Type  | aM                         |