

18544008

Automatic transfer switch ATyS g M 4P 80A in steel enclosure IP3X



Strong points

- Quick installation
- Wide choice
- Low-maintenance
- Adaptability

General characteristics

- Suitable for an environment subject to mechanical risk and dust hazards (IP54 version).
 - Bridging bars included.
 - IP/IK protection rating: IP3x (no cutout) or IP54 (with window).
 - Colour: RAL 7035.
 - Cable gland steel that can be removed top and bottom.
 - Connection: bottom/top with ATyS g M and ATyS p M (bottom input/top output)
 - Material: 1.2 mm steel.
- Coating: epoxy polyester powder.
- Mounting: 4 unmounted wall fixing lugs.
 - Hinged door with double 3 mm bolt.
 - Door cutout (IP3x)/Window (IP54): 327 x 47 mm.

Compliance with standards

- IEC 60947-3
- IEC 60947-6-1
- IEC 61439-2

Link to the reference

<https://apac.socomec.com/en/reference/18544008>

Our transfer enclosures are equipped with ATyS motorised or automatic transfer switches to ensure power availability in critical applications. The motorised transfer enclosures can be remotely controlled via dry contacts (e.g. via an external control system or pushbuttons). The automatic transfer enclosures monitor the status of the low-voltage power sources and provide full autonomous management of the power availability.

----- System -----	
Fill rate E-Order Common	71
Fill rate E-Order Selection	100
Classification	
UNSPSC	39122205
ETIM Class	EC000216
IGCC	5177
Commerce	
Effective date	2010-04-16
Country of origin	FR
Discount Policy	1CM44
Discount Policy Label	ENCL.MOTORISED COS
Length of the product unit	0.6
Width of the product unit	0.45
Depth of the product unit	0.2
ETIM - Electrical characteristics	
Max. rated operation voltage Ue AC [V]	400
Rated operating voltage [V]	230..400
Rated permanent current Iu [A]	80
Rated permanent current at AC-23, 400 V [A]	80
Rated permanent current at AC-21, 400 V [A]	80
Rated short-time withstand current Icw [kA]	4
Rated operation power at AC-23, 400 V [kW]	80
Conditioned rated short-circuit current Iq [kA]	50
Number of poles	4
ETIM - Mechanical characteristics	
Suitable for floor mounting	No
Degree of protection (IP), front side	IP3X
ETIM - Technical features	
Version as main switch	Yes
Version as maintenance-/service switch	Yes
Version as safety switch	Yes
Version as emergency stop installation	No
Version as reversing switch	Yes
Number of switches	2
Number of auxiliary contacts as change-over contact	3
Motor drive optional	No
Motor drive integrated	Yes
Voltage release optional	No
Device construction	Complete device in housing
Type of control element	Other

Interlockable	Yes
Type of electrical connection of main circuit	Screw connection
Logistics	
GTIN/EAN	3596032004378
Customs number	8536508090
Price unit	PC
Weight of the packing unit	14
Length of the packing unit	0.62
Width of the packing unit	0.42
Depth of the packing unit	0.22
Norms	
Conformity to standards	IEC
Technical Characteristics	
Control operator	Automatic programmable for Genset
Number of poles	4
Rated current	80
Frame size	ATYS M