

**192T0612**

## Primary wound moulded case CT TRB 135 125A/5A Class 0,5 10VA



### Strong points

- Compatible accuracy class
- Wide range of ratings and dimensions
- Quick and easy to install

### General characteristics

- Accuracy class: 0.2s — 0.5 or 1.
- Dielectric quality: 3 kV — 50 Hz — 1 min.
- Operating frequency: 50 — 60 Hz.
- Permanent overload: 1.2 In.
- Insulation class: E (120 °C).

### Compliance with standards

- IEC 61869-2
- IEC 61439-1

### Link to the reference

Current transformers deliver to the secondary a standard current proportional to the primary current and adapted to the rating of the associated device. They are equipped as standard with removable terminal covers and double terminals allowing the secondary to be short-circuited without any risk.

They are mounted using two screw-on metal brackets or, in certain cases, by a clip-on DINrail fastener. The connections are made by screws or by fast-on terminals.

### Classification

UNSPSC	39121032
ETIM Class	EC002048
IGCC	4186

### Commerce

Effective date	1998-02-09
Country of origin	DE

### ETIM - Electrical characteristics

Rated primary current [A]	125
Rated secondary current [A]	5
Rated secondary apparent power [VA]	10
Accuracy class	0.5
Overcurrent limiting factor	FS 5
Calibrated	No

### ETIM - Mechanical characteristics

With contact protection	No
Snap mounting	Yes
With copper rail	Yes
Secondary connection	Screw connection

### ETIM - Technical features

Model	Wound primary current converter
Number of primary inputs	1

### Logistics

GTIN/EAN	3596031090211
Customs number	8504318090
Price unit	PC
Weight of the packing unit	1.13
Length of the packing unit	0.08
Width of the packing unit	0.1
Depth of the packing unit	0.14

### Technical Characteristics

Model	TRB 135
Rated current	125
Secondary rated current	5

<https://apac.socomec.com/en/reference/192T0612>