

192T2106

Bar or cable-through CT TCB 17-20 60A/5A Class 1 1VA



Strong points

- Compatible accuracy class
- Wide range of ratings and dimensions
- Quick and easy to install

General characteristics

- Accuracy class: 0.2s — 0.5 or 1.
- Dielectric quality: 3 kV — 50 Hz — 1 min.
- Operating frequency: 50 — 60 Hz.
- Permanent overload: 1.2 In.
- Insulation class: E (120 °C).

Compliance with standards

- IEC 61869-2
- IEC 61439-1

Link to the reference

<https://apac.socomec.com/en/reference/192T2106>

Current transformers deliver to the secondary a standard current proportional to the primary current and adapted to the rating of the associated device. They are equipped as standard with removable terminal covers and double terminals allowing the secondary to be short-circuited without any risk.

They are mounted using two screw-on metal brackets or, in certain cases, by a clip-on DINrail fastener. The connections are made by screws or by fast-on terminals.

Classification	
UNSPSC	39121032
ETIM Class	EC002048
IGCC	4186
Commerce	
Effective date	1998-02-09
Country of origin	DE
ETIM - Electrical characteristics	
Rated primary current [A]	60
Rated secondary current [A]	5
Rated secondary apparent power [VA]	1
Accuracy class	1
Overcurrent limiting factor	FS 5
Calibrated	Yes
ETIM - Mechanical characteristics	
With contact protection	Yes
Height opening [mm]	20..20
Width opening [mm]	20..20
Opening diameter [mm]	17.5
Snap mounting	Yes
With copper rail	No
Secondary connection	Screw connection
ETIM - Technical features	
Model	Through-feed current converter
Number of primary inputs	1
Logistics	
GTIN/EAN	3596031091027
Customs number	8504318090
Price unit	PC
Weight of the packing unit	0.23
Length of the packing unit	0.085
Width of the packing unit	0.055
Depth of the packing unit	0.055
Norms	
Conformity to standards	IEC
Technical Characteristics	
Model	TCB 17-20
Opening	20x5 - Diam.17,5
Rated current	60
Secondary rated current	5