


21PV3822

Load break switch photovoltaic applications SIRCO MC PV 1000VDC 2 P+, 1 P- 25A



Link to the reference

<https://apac.socomec.com/en/reference/21PV3822>

----- System -----

Fill rate E-Order Common	100
Fill rate E-Order Selection	78

Classification

UNSPSC	39122233
ETIM Class	EC000216
IGCC	5290

Commerce

Effective date	2012-01-14
Obsolescence date	2021-06-01
Production ban date	2021-12-31
Country of origin	PL
Discount Policy	1CD20
Discount Policy Label	INTER PV IEC
Length of the product unit	0.055
Width of the product unit	0.0445
Depth of the product unit	0.051
Weight	0.19

ETIM - Electrical characteristics

Max. rated operation voltage Ue AC [V]	1000
Rated operating voltage [V]	600..1000
Rated permanent current Iu [A]	25
Number of poles	3

### ETIM - Mechanical characteristics

Suitable for floor mounting	No
Suitable for front mounting 4-hole	No
Suitable for front mounting centre	Yes
Suitable for distribution board installation	Yes
Suitable for intermediate mounting	Yes
Colour control element	Other
Degree of protection (IP), front side	IP20

### ETIM - Technical features

Version as main switch	Yes
Version as maintenance-/service switch	Yes
Version as safety switch	Yes
Version as emergency stop installation	Yes
Version as reversing switch	No
Number of switches	1
Motor drive optional	No
Motor drive integrated	No
Voltage release optional	No
Device construction	Built-in device fixed built-in technique
Type of control element	Other
Interlockable	Yes
Type of electrical connection of main circuit	Screw connection

### Logistics

GTIN/EAN	3596032794941
Customs number	8536508090
Price unit	PC
Weight of the packing unit	0.19
Length of the packing unit	0.09
Width of the packing unit	0.08
Depth of the packing unit	0.08

### Norms

Conformity to standards	IEC UL
-------------------------	------------

### Technical Characteristics

Control operator	Manual
Number of poles	3
Rated voltage	1000
Rated current	25
Type	Frontal operation
Frame size	MC