

22013006

Load break switch standards UL and CSA SIRCO M 3P 60A



Strong points

- Fully integrated
- A wide range of accessories
- Upgradeability
- Compliance with major certifications and approvals

General characteristics

- Double break by phase.
- Mount on DIN rail, panel or modular panel with 45 mm front cut out.
- IP20 accessories and device.
- Extreme usage categories (AC-22 and AC-23).
- Clear break indication.
- Contact point technology.
- Standard device attaches from the front using the "door mounting kit".

Compliance with standards

- IEC 60947-3
- UL 508, UL98
- GB/T 14048.3

Link to the reference

<https://apac.socomec.com/en/reference/22013006>

SIRCO M are manually operated modifiable and modular multipolar load break switches.

They make and break under load conditions and provide safety isolation for any low voltage circuit, particularly for machine control circuits.

Through the use of accessories, SIRCO M can be transformed into multipolar load break or 3/4 pole changeover switches provide on load changeover switching between two sources or two low voltage power circuits, as well as their safety isolation.

Classification

UNSPSC	39122233
ETIM Class	EC000216
IGCC	5290

Commerce

Effective date	2009-09-07
Country of origin	CN
Length of the product unit	0.189
Width of the product unit	0.078
Depth of the product unit	0.075
Weight	0.63

ETIM - Electrical characteristics

Max. rated operation voltage Ue AC [V]	690
Rated operating voltage [V]	400..690
Rated permanent current Iu [A]	60
Rated permanent current at AC-23, 400 V [A]	60
Rated permanent current at AC-21, 400 V [A]	60
Rated short-time withstand current Icw [kA]	2.75
Rated operation power at AC-23, 400 V [kW]	60
Switching power at 400 V [kW]	60
Conditioned rated short-circuit current Iq [kA]	50
Number of poles	3

ETIM - Mechanical characteristics

Suitable for floor mounting	No
Suitable for front mounting 4-hole	No
Suitable for front mounting centre	No
Suitable for distribution board installation	Yes
Suitable for intermediate mounting	Yes
Colour control element	Other
Degree of protection (IP), front side	IP20

ETIM - Technical features

Version as main switch	Yes
Version as maintenance-/service switch	Yes
Version as safety switch	Yes
Version as emergency stop installation	Yes
Version as reversing switch	No
Number of switches	1
Motor drive optional	No
Motor drive integrated	No
Voltage release optional	No

Device construction	Built-in device fixed built-in technique
Type of control element	Other
Interlockable	Yes
Type of electrical connection of main circuit	Screw connection
Logistics	
GTIN/EAN	3596031973743
Customs number	8536508090
Price unit	PC
Weight of the packing unit	0.63
Length of the packing unit	0.17
Width of the packing unit	0.1
Depth of the packing unit	0.09
Norms	
Conformity to standards	IEC UL
Technical Characteristics	
Control operator	Direct : M01 / External : S00, S0, S01
Number of poles	3
Rated voltage	690 VAC - 400 VDC
Rated current	60
Type	Rotary
Frame size	M3