


22303010

Universal load break switch body SIRCO M 3P 100A



Strong points

- Secured breaking
- Modular device
- Improved on-load switching

General characteristics

- Range from 25A to 125A.
- Available in 3P or 4P.
- Direct handle or external handle.

Compliance with standards

- IEC 60947-3

Link to the reference

<https://apac.socomec.com/en/reference/22303010>

SIRCO M are manually operated 3 or 4 pole modular transfer switches with positive break indication. They provide on-load transfer between two sources for any low voltage power circuit, as well as safety isolation. Other applications include source inversion (e.g. to change the direction of a motor) or grounding/earthing.

Classification

UNSPSC	39122205
ETIM Class	EC000216
IGCC	5177

Commerce

Effective date	2011-03-17
Country of origin	FR
Length of the product unit	0.1245
Width of the product unit	0.159
Depth of the product unit	0.1
Weight	1.48

ETIM - Electrical characteristics

Max. rated operation voltage Ue AC [V]	800
Rated operating voltage [V]	400..690
Rated permanent current Iu [A]	100
Rated permanent current at AC-23, 400 V [A]	100
Rated permanent current at AC-21, 400 V [A]	100
Rated short-time withstand current Icw [kA]	2.75
Rated operation power at AC-23, 400 V [kW]	45
Switching power at 400 V [kW]	45
Conditioned rated short-circuit current Iq [kA]	25
Number of poles	3

ETIM - Mechanical characteristics

Suitable for floor mounting	No
Suitable for front mounting 4-hole	No
Suitable for front mounting centre	No
Suitable for distribution board installation	Yes
Suitable for intermediate mounting	Yes
Colour control element	Black
Degree of protection (IP), front side	IP20

ETIM - Technical features

Version as main switch	Yes
Version as maintenance-/service switch	Yes
Version as safety switch	Yes
Version as emergency stop installation	No
Version as reversing switch	Yes
Number of switches	2
Motor drive optional	No
Motor drive integrated	No
Voltage release optional	No
Device construction	Built-in device fixed built-in technique
Type of control element	Short thumb-grip
Interlockable	Yes
Type of electrical connection of main circuit	Screw connection

Logistics	
GTIN/EAN	3596032045692
Customs number	8536508090
Price unit	PC
Weight of the packing unit	1.48
Length of the packing unit	0.24
Width of the packing unit	0.18
Depth of the packing unit	0.1
Norms	
Conformity to standards	IEC
Technical Characteristics	
Number of poles	3
Rated current	100
Frame size	M3