

**21154412**

## Load break switch COMO 4P 125A enclosed yellow/red handle



### Strong points

- Safe operation
- Suitable for all kinds of environment
- Easy installation
- Range

### General characteristics

- From 20 to 125 A.
- 3, 4, 6, 8 poles.
- Yellow/red or grey/blue version.
- Triple lock in OFF position.
- Polycarbonate enclosure.
- Screw-on front.
- Degree of protection: IP65.
- Cable gland knockouts at top, bottom and sides.
- Switch centring system for easy closing.
- Door interlocking when switch is ON.

### Compliance with standards

- IEC 60947-3

### Link to the reference

<https://apac.socomec.com/en/reference/21154412>

Enclosed load break switches ensure the on-load breaking and making of circuits and safely isolate all low-voltage electrical circuits by providing protection against contact with live parts and environmental elements, such as dust, water and other hazards.

They enable the shutdown and lock out of the power supply as close to the equipment as possible.

Classification	
UNSPSC	39122205
ETIM Class	EC000216
IGCC	5176
Commerce	
Effective date	2017-01-16
Country of origin	DE
Length of the product unit	0.304
Width of the product unit	0.214
Depth of the product unit	0.182
Weight	1.71
ETIM - Electrical characteristics	
Max. rated operation voltage Ue AC [V]	690
Rated operating voltage [V]	400..690
Rated permanent current Iu [A]	125
Rated permanent current at AC-23, 400 V [A]	84
Rated permanent current at AC-21, 400 V [A]	125
Rated operation power at AC-3, 400 V [kW]	125
Rated short-time withstand current Icw [kA]	2
Rated operation power at AC-23, 400 V [kW]	45
Switching power at 400 V [kW]	45
Conditioned rated short-circuit current Iq [kA]	8
Number of poles	4
ETIM - Mechanical characteristics	
Suitable for floor mounting	Yes
Suitable for front mounting 4-hole	No
Suitable for front mounting centre	No
Suitable for distribution board installation	No
Suitable for intermediate mounting	No
Colour control element	Red
Degree of protection (IP), front side	IP65
ETIM - Technical features	
Version as main switch	No
Version as maintenance-/service switch	Yes
Version as safety switch	Yes
Version as emergency stop installation	Yes
Version as reversing switch	No
Number of switches	1
Motor drive optional	No
Motor drive integrated	No
Voltage release optional	No
Device construction	Complete device in housing

Type of control element	Door coupling rotary drive
Interlockable	Yes
Type of electrical connection of main circuit	Screw connection
<b>Logistics</b>	
GTIN/EAN	3596033000751
Customs number	8537109899
Price unit	PC
Weight of the packing unit	1.71
Length of the packing unit	0.225
Width of the packing unit	0.195
Depth of the packing unit	0.31
<b>Norms</b>	
Conformity to standards	IEC
<b>Technical Characteristics</b>	
Control operator	Yellow / red handle
Number of poles	4
Rated current	125
Type	Rotary
Frame size	3