

**32733160**

## **Steel safety enclosure 3P 1600A with bottom/bottom connection side operation**



### **Strong points**

- Operator safety
- Quick and easy implementation
- Durability
- Operating continuity
- Inductive load breaking (AC23)

### **General characteristics**

- Robust steel sheet safety enclosure.
- Equipped with SIDER visible load break switches.
- Metal operating handle.
- Double locking.
- Auxiliary control.
- Cables are connected either to cage terminals or directly to the terminals.

### **Compliance with standards**

- IEC 60947-3
- IEC 61439-2
- IEC 60204-1
- IEC 60364

### **Link to the reference**

<https://apac.socomec.com/en/reference/32733160>

Safety enclosures equipped with SOCOMEC switches provide emergency breaking, breaking for mechanical maintenance, safety isolation and lock out in the vicinity of any low voltage final circuit.

<b>Classification</b>	
UNSPSC	39122205
ETIM Class	EC000216
IGCC	5176
<b>Commerce</b>	
Effective date	2019-10-01
Country of origin	FR
<b>ETIM - Electrical characteristics</b>	
Max. rated operation voltage Ue AC [V]	690
Rated operating voltage [V]	400..690
Rated permanent current Iu [A]	1600
Rated permanent current at AC-21, 400 V [A]	1600
Rated operation power at AC-3, 400 V [kW]	1600
Number of poles	3
<b>ETIM - Mechanical characteristics</b>	
Suitable for floor mounting	No
Suitable for front mounting 4-hole	Yes
Suitable for front mounting centre	No
Suitable for distribution board installation	No
Suitable for intermediate mounting	No
Colour control element	Red
Degree of protection (IP), front side	IP65
<b>ETIM - Technical features</b>	
Version as main switch	No
Version as maintenance-/service switch	Yes
Version as safety switch	Yes
Version as emergency stop installation	Yes
Version as reversing switch	No
Number of switches	1
Motor drive optional	No
Motor drive integrated	No
Voltage release optional	No
Device construction	Complete device in housing
Type of control element	Door coupling rotary drive
Interlockable	Yes
Type of electrical connection of main circuit	Bolt connection
<b>Logistics</b>	
GTIN/EAN	3596033018831
Customs number	8536508090
Price unit	PC
Weight of the packing unit	0.01
<b>Norms</b>	
Conformity to standards	IEC

Technical Characteristics

Control operator	Side
Number of poles	3
Rated current	1600
Type	Steel safety enclosure