


**22053003**

## Universal load break switch SIRCO M 3P 32A toggle switch



### Strong points

- Fully integrated
- A wide range of accessories
- Upgradeability
- Compliance with major certifications and approvals

### General characteristics

- Double break by phase.
- Mount on DIN rail, panel or modular panel with 45 mm front cut out.
- IP20 accessories and device.
- Extreme usage categories (AC-22 and AC-23).
- Clear break indication.
- Contact point technology.
- Standard device attaches from the front using the "door mounting kit".

### Compliance with standards

- IEC 60947-3
- UL 508, UL98
- GB/T 14048.3

### Link to the reference

<https://apac.socomec.com/en/reference/22053003>

SIRCO M are manually operated modifiable and modular multipolar load break switches. They make and break under load conditions and provide safety isolation for any low voltage circuit, particularly for machine control circuits. Through the use of accessories, SIRCO M can be transformed into multipolar load break or 3/4 pole changeover switches provide on load changeover switching between two sources or two low voltage power circuits, as well as their safety isolation.

<b>Classification</b>	
UNSPSC	39122233
ETIM Class	EC000216
IGCC	5290
<b>Commerce</b>	
Effective date	2006-04-13
Country of origin	CN
Length of the product unit	0.068
Width of the product unit	0.045
Depth of the product unit	0.064
Weight	0.232
<b>ETIM - Electrical characteristics</b>	
Max. rated operation voltage Ue AC [V]	690
Rated operating voltage [V]	400..690
Rated permanent current Iu [A]	32
Rated permanent current at AC-23, 400 V [A]	32
Rated permanent current at AC-21, 400 V [A]	32
Rated short-time withstand current Icw [kA]	1.26
Rated operation power at AC-23, 400 V [kW]	15
Switching power at 400 V [kW]	15
Conditioned rated short-circuit current Iq [kA]	50
Number of poles	3
<b>ETIM - Mechanical characteristics</b>	
Suitable for floor mounting	No
Suitable for front mounting 4-hole	No
Suitable for front mounting centre	No
Suitable for distribution board installation	Yes
Suitable for intermediate mounting	Yes
Colour control element	Black
Degree of protection (IP), front side	IP20
<b>ETIM - Technical features</b>	
Version as main switch	Yes
Version as maintenance-/service switch	Yes
Version as safety switch	Yes
Version as emergency stop installation	Yes
Version as reversing switch	No
Number of switches	1
Motor drive optional	No
Motor drive integrated	No
Voltage release optional	No

Device construction	Built-in device fixed built-in technique
Type of control element	Toggle
Interlockable	Yes
Type of electrical connection of main circuit	Screw connection
<b>Logistics</b>	
GTIN/EAN	3596031825509
Customs number	8536508090
Price unit	PC
Weight of the packing unit	0.232
Length of the packing unit	0.105
Width of the packing unit	0.06
Depth of the packing unit	0.085
<b>Norms</b>	
Conformity to standards	IEC UL
<b>Technical Characteristics</b>	
Control operator	Toggle
Number of poles	3
Rated voltage	690 VAC - 400 VDC
Rated current	32
Type	Toggle
Frame size	M1