

**36152006**

## Switch-discon-fuse FUSERBLOC-Dir R OP-63A-2P-DIN-Fuse S00C

### Strong points

- Improved safety
- High breaking capacity
- Specific functionalities for simplified use

### General characteristics

- 25 to 400 A.
- Up to 690 VAC.
- Up to 100 kA.
- Available in 2P, 3P or 4P from 25 to 400.

### Compliance with standards

- IEC 60947-3
- IEC 60269-1
- IEC 60269-2

### Link to the reference

<https://apac.socomec.com/en/reference/36152006>

FUSERBLOC are manually operated multipolar fuse combination switches. They make and break on load and provide safety isolation and protection against overcurrent for any low voltage electrical circuit.

### Classification

UNSPSC	39122233
ETIM Class	EC001040
IGCC	5291

### Commerce

Effective date	1991-06-03
Obsolescence date	2023-12-30
Production ban date	2024-03-30
Country of origin	FR
Length of the product unit	0.118
Width of the product unit	0.133
Depth of the product unit	0.134
Weight	0.88

### ETIM - Electrical characteristics

Max. rated operation voltage Ue AC [V]	690
Rated permanent current Iu [A]	63
Rated operation power at AC-23, 400 V [kW]	30
Conditioned rated short-circuit current Iq [kA]	100
Number of poles	2

### ETIM - Mechanical characteristics

Cable entry	Top/bottom
Equipped with connectors	No
Suitable for floor mounting	Yes
Suitable for front mounting	Yes
Suitable for busbar mounting	No
Degree of protection (IP), front side	IP20

### ETIM - Technical features

Version as main switch	Yes
Version as safety switch	Yes
Suitable for fuses	NHC00
With error protection	No
Type of electrical connection of main circuit	Frame clamp
Type of control element	Rocker lever
Position control element	Right
Motor drive optional	No
Motor drive integrated	No
Version as emergency stop installation	Yes

### Logistics

GTIN/EAN	3596031174850
Customs number	8536303099
Price unit	PC
Weight of the packing unit	0.988
Length of the packing unit	0.195
Width of the packing unit	0.145

Depth of the packing unit	0.13
<b>Norms</b>	
Conformity to standards	IEC
<b>Technical Characteristics</b>	
Fuse size	NH00C
Number of poles	2
Rated current	63
Type	I-0
Frame size	2