

36256021

Switch-discon-fuse FUSERBLOC W/O handle-L R OP-200A-4P-BS-Fuse B1-B2

Strong points

- Improved safety
- High breaking capacity
- Multi-use
- Simplified use

General characteristics

- For industrial fuses up to 1250 A.
- 2P, 3P or 4P available.
- Up to 690 VAC.
- Up to 100 kA.

Compliance with standards

- IEC 60947-3
- BS EN 60947-3
- IEC 60269-1
- IEC 60269-2

Link to the reference



<https://apac.socomec.com/en/reference/36256021>

FUSERBLOC BS 88 units with right front-side operation are manually-operated multipole fuse load break switches.

They provide make and break on load and safety isolation and protection against overcurrent for any low voltage electrical circuit.

This range is available in direct and external operation, in 2, 3 and 4 poles and up to 1250 A.

Classification

UNSPSC	39122233
ETIM Class	EC001040
IGCC	5291

Commerce

Effective date	1998-06-09
Obsolescence date	2023-06-30
Production ban date	2023-12-30
Country of origin	FR
Discount Policy	1CC44
Discount Policy Label	FUSERBLOC MODUL BS
Length of the product unit	0.195
Width of the product unit	0.313
Depth of the product unit	0.173
Weight	4.15

ETIM

Version as main switch	Yes
Version as safety switch	Yes
Max. rated operation voltage Ue AC [V]	690
Rated permanent current Iu [A]	200
Rated operation power at AC-23, 400 V [kW]	63
Conditioned rated short-circuit current Iq [kA]	100
Suitable for fuses	Shape A4
Number of poles	4
With error protection	No
Type of electrical connection of main circuit	Bolt connection
Cable entry	Top/bottom
Equipped with connectors	No
Suitable for floor mounting	Yes
Suitable for front mounting	Yes
Suitable for busbar mounting	No
Type of control element	Rocker lever
Position control element	Right
Motor drive optional	No
Motor drive integrated	No
Version as emergency stop installation	Yes
Degree of protection (IP), front side	IP20

Logistics

GTIN/EAN	3596031179800
Customs number	8536309090
Price unit	PC

Weight of the packing unit	4.15
Norms	
Conformity to standards	IEC
Technical Characteristics	
Fuse size	B1-B2
Number of poles	4
Rated current	200
Type	I-0
Frame size	5