

26PV2031

DC LOAD BREAK SWITCH SIRCO PV IEC 315A 2P 1000VDC B4



Strong points

- Optimise your investment
- High quality materials
- Take advantage of an innovative design
- Reliability and performance

General characteristics

- Patented switching technology up to 500 VDC/pole.
- Positive indication.
- Up to 1500 VDC according to IEC 60947-3.

Compliance with standards

- IEC 60947-3
- IEC 60364-7-712
- UL 98B

Link to the reference

<https://apac.socomec.com/en/reference/26PV2031>

SIRCO PV are manually operated load break switches.
 Making and breaking capacity under load conditions up to 1500 VDC.
 These extremely durable switches have been tested and approved for use in the most demanding applications.
 They have been designed and tested for all types of applications: grounded, floating or bipolar.

----- System -----

Fill rate E-Order Common	86
Fill rate E-Order Selection	78

Classification

UNSPSC	39122233
ETIM Class	EC000216
IGCC	5290

Commerce

Effective date	2013-07-15
Country of origin	TN
Discount Policy	1CD20
Discount Policy Label	INTER PV IEC
Length of the product unit	0.17
Width of the product unit	0.23
Depth of the product unit	0.079
Weight	1.85

ETIM - Electrical characteristics

Max. rated operation voltage Ue AC [V]	1000
Rated operating voltage [V]	400..415
Rated permanent current Iu [A]	315
Rated short-time withstand current Icw [kA]	5
Number of poles	2

ETIM - Mechanical characteristics

Suitable for floor mounting	No
Suitable for front mounting 4-hole	No
Suitable for front mounting centre	No
Suitable for distribution board installation	No
Suitable for intermediate mounting	Yes
Colour control element	Other
Degree of protection (IP), front side	IP20

ETIM - Technical features

Version as main switch	Yes
Version as maintenance-/service switch	Yes
Version as safety switch	Yes
Version as emergency stop installation	Yes
Version as reversing switch	No
Number of switches	1
Motor drive optional	No
Motor drive integrated	No
Voltage release optional	No
Device construction	Built-in device fixed built-in technique
Type of control element	Other

Interlockable	Yes
Type of electrical connection of main circuit	Bolt connection
Logistics	
GTIN/EAN	3596032760441
Customs number	8536508090
Price unit	PC
Weight of the packing unit	1.85
Length of the packing unit	0.21
Width of the packing unit	0.166
Depth of the packing unit	0.155
Norms	
Conformity to standards	CCC IEC
Technical Characteristics	
Control operator	Direct : B2, J1 / External : S2
Number of poles	2
Rated voltage	1000
Rated current	315
Type	Frontal operation
Frame size	B4