

**36314003**

## Switch-discon-fuse FUSERBLOC CD-Ext&Dir F/L R&L OP-32A-3+NC-NFC-Fuse 10x38



### Strong points

- Improved safety
- High breaking capacity
- Multi-use
- Specific functionalities for simplified use

### General characteristics

- 25 to 1250 A.
- Up to 690 VAC.
- Up to 100 kA.
- Available in 2P, 3P or 4P, from 25 to 1250 A.

### Compliance with standards

- IEC 60947-3
- IEC 60269-1
- IEC 60269-2

### Link to the reference

<https://apac.socomec.com/en/reference/36314003>

Front/side control FUSERBLOCs are manually operated multipolar fuse load break switches.

They make and break on load and provide safety isolation and protection against overcurrent for any low voltage electrical circuit.

This range includes both direct and external-control models, with 2, 3 and 4 poles and from 25 to 1250 A.

#### ----- System -----

Fill rate E-Order Common	86
Fill rate E-Order Selection	100

#### Classification

UNSPSC	39122233
ETIM Class	EC001040
IGCC	5291

#### Commerce

Effective date	1998-11-20
Country of origin	FR
Discount Policy	1CC22
Discount Policy Label	FUSERBLOC CD NFC
Length of the product unit	0.098
Width of the product unit	0.096
Depth of the product unit	0.112
Weight	0.5

#### ETIM - Electrical characteristics

Max. rated operation voltage Ue AC [V]	690
Rated permanent current Iu [A]	32
Rated operation power at AC-23, 400 V [kW]	15
Conditioned rated short-circuit current Iq [kA]	100
Number of poles	4

#### ETIM - Mechanical characteristics

Cable entry	Top/bottom
Equipped with connectors	No
Suitable for floor mounting	Yes
Suitable for front mounting	Yes
Suitable for busbar mounting	No
Degree of protection (IP), front side	IP20

#### ETIM - Technical features

Version as main switch	Yes
Version as safety switch	Yes
Suitable for fuses	10x38 mm
With error protection	No
Type of electrical connection of main circuit	Frame clamp
Type of control element	Short thumb-grip
Position control element	Front side
Motor drive optional	No
Motor drive integrated	No
Version as emergency stop installation	Yes

### Logistics

GTIN/EAN	3596031183715
Customs number	8536303099
Price unit	PC
Weight of the packing unit	0.5
Length of the packing unit	0.115
Width of the packing unit	0.09
Depth of the packing unit	0.115

### Norms

Conformity to standards	IEC UL
-------------------------	------------

### Technical Characteristics

Control operator	Direct : P1 / External : S1
Fuse size	10x38
Number of poles	3+NC
Rated current	32
Type	I-0-Test