

**36414001**

## Switch-discon-fuse CD FUSERBLOC-Ext&Dir F/L R&L OP-32A-3+NC-BS-Fuse A1

### Strong points

- Improved safety
- High breaking capacity
- Multi-use
- Simplified use

### General characteristics

- For industrial fuses up to 1250 A.
- 2P, 3P or 4P available.
- Up to 690 VAC.
- Up to 100 kA.

### Compliance with standards

- IEC 60947-3
- BS EN 60947-3
- IEC 60269-1
- IEC 60269-2

### Link to the reference

FUSERBLOC BS 88 units with right front-side operation are manually-operated multipole fuse load break switches.

They provide make and break on load and safety isolation and protection against overcurrent for any low voltage electrical circuit.

This range is available in direct and external operation, in 2, 3 and 4 poles and up to 1250 A.

### Classification

UNSPSC	39122233
ETIM Class	EC001040
IGCC	5291

### Commerce

Effective date	1998-11-20
Country of origin	FR
Length of the product unit	0.098
Width of the product unit	0.192
Depth of the product unit	0.083
Weight	0.53

### ETIM - Electrical characteristics

Max. rated operation voltage Ue AC [V]	690
Rated permanent current Iu [A]	32
Rated operation power at AC-23, 400 V [kW]	15
Conditioned rated short-circuit current Iq [kA]	80
Number of poles	4

### ETIM - Mechanical characteristics

Cable entry	Top/bottom
Equipped with connectors	No
Suitable for floor mounting	Yes
Suitable for front mounting	Yes
Suitable for busbar mounting	No
Degree of protection (IP), front side	IP20

### ETIM - Technical features

Version as main switch	Yes
Version as safety switch	Yes
With error protection	No
Type of electrical connection of main circuit	Frame clamp
Type of control element	Long turning handle
Position control element	Front side
Motor drive optional	No
Motor drive integrated	No
Version as emergency stop installation	Yes

### Logistics

GTIN/EAN	3596031184941
Customs number	8536303099
Price unit	PC
Weight of the packing unit	0.53
Length of the packing unit	0.12

<https://apac.socomec.com/en/reference/36414001>

Width of the packing unit	0.095
Depth of the packing unit	0.1
<b>Norms</b>	
Conformity to standards	IEC
<b>Technical Characteristics</b>	
Control operator	Direct : P1 / External : S1
Fuse size	A1
Number of poles	3+NC
Rated current	32
Type	I-O-Test