

26PV6200

DC LOAD BREAK SWITCH SIRCO PV IEC 2000A 6P 1200VDC B7 ds

Strong points

- Optimise your investment
- High quality materials
- Take advantage of an innovative design
- Reliability and performance

General characteristics

- Patented switching technology up to 500 VDC/pole.
- Positive indication.
- Up to 1500 VDC according to IEC 60947-3.

Compliance with standards

- IEC 60947-3
- IEC 60364-7-712
- UL 98B

Link to the reference

SIRCO PV are manually operated load break switches.

Making and breaking capacity under load conditions up to 1500 VDC.

These extremely durable switches have been tested and approved for use in the most demanding applications.

They have been designed and tested for all types of applications: grounded, floating or bipolar.

Classification

UNSPSC	39122233
ETIM Class	EC000216
IGCC	5290

Commerce

Effective date	2012-11-19
Obsolescence date	2021-07-01
Production ban date	2021-12-31
Country of origin	FR

ETIM - Electrical characteristics

Rated permanent current Iu [A]	2000
Number of poles	6

ETIM - Mechanical characteristics

Suitable for floor mounting	No
Suitable for front mounting 4-hole	No
Suitable for front mounting centre	No
Suitable for distribution board installation	No
Suitable for intermediate mounting	Yes
Colour control element	Other
Degree of protection (IP), front side	IP20

ETIM - Technical features

Version as main switch	Yes
Version as maintenance-/service switch	Yes
Version as safety switch	Yes
Version as emergency stop installation	Yes
Version as reversing switch	No
Number of switches	1
Motor drive optional	No
Motor drive integrated	No
Voltage release optional	No
Device construction	Built-in device fixed built-in technique
Type of control element	Other
Interlockable	Yes
Type of electrical connection of main circuit	Bolt connection

Logistics

GTIN/EAN	3596032713362
Customs number	8536508090
Price unit	PC
Weight of the packing unit	50
Length of the packing unit	0.54
Width of the packing unit	0.6
Depth of the packing unit	0.8

<https://apac.socomec.com/en/reference/26PV6200>

Norms	
Conformity to standards	CCC IEC
Technical Characteristics	
Control operator	Manual
Number of poles	6
Rated voltage	1200
Rated current	2000
Type	Frontal operation
Frame size	B7ds