

36415000

Switch-discon-fuse CD FUSERBLOC-Ext&Dir F/L R&L OP-20A-3+NP-BS-Fuse A1



Strong points

- Improved safety
- High breaking capacity
- Multi-use
- Simplified use

General characteristics

- For industrial fuses up to 1250 A.
- 2P, 3P or 4P available.
- Up to 690 VAC.
- Up to 100 kA.

Compliance with standards

- IEC 60947-3
- BS EN 60947-3
- IEC 60269-1
- IEC 60269-2

Link to the reference

<https://apac.socomec.com/en/reference/36415000>

FUSERBLOC BS 88 units with right front-side operation are manually-operated multipole fuse load break switches. They provide make and break on load and safety isolation and protection against overcurrent for any low voltage electrical circuit. This range is available in direct and external operation, in 2, 3 and 4 poles and up to 1250 A.

----- System -----

Fill rate E-Order Common	100
Fill rate E-Order Selection	100
Classification	
UNSPSC	39122233
ETIM Class	EC001040
IGCC	5291
Commerce	
Effective date	1998-11-20
Country of origin	FR
Discount Policy	1CC42
Discount Policy Label	FUSERBLOC CD BS
Length of the product unit	0.098
Width of the product unit	0.192
Depth of the product unit	0.083
Weight	0.552
ETIM - Electrical characteristics	
Max. rated operation voltage Ue AC [V]	690
Rated permanent current Iu [A]	20
Rated operation power at AC-23, 400 V [kW]	9
Conditioned rated short-circuit current Iq [kA]	100
Number of poles	4
ETIM - Mechanical characteristics	
Cable entry	Top/bottom
Equipped with connectors	No
Suitable for floor mounting	Yes
Suitable for front mounting	Yes
Suitable for busbar mounting	No
Degree of protection (IP), front side	IP20
ETIM - Technical features	
Version as main switch	Yes
Version as safety switch	Yes
Suitable for fuses	Other
With error protection	No
Type of electrical connection of main circuit	Frame clamp
Type of control element	Long turning handle
Position control element	Front side
Motor drive optional	No
Motor drive integrated	No
Version as emergency stop installation	Yes

Logistics

GTIN/EAN	3596031185047
Customs number	8536303099
Price unit	PC
Weight of the packing unit	0.552
Length of the packing unit	0.089
Width of the packing unit	0.105
Depth of the packing unit	0.118

Norms

Conformity to standards	IEC
-------------------------	-----

Technical Characteristics

Control operator	Direct : P1 / External : S1
Fuse size	A1
Number of poles	3+NP
Rated current	20
Type	I-0-Test