

29054013

AC Load break switch with visible contacts SIDER 4P 125A side operation

Strong points

- Increased safety with visible breaking
- Modularity

General characteristics

- 125A to 3150A.
- 3P or 4P available.
- Direct or external handle.
- Auxiliary contact optional.

Compliance with standards

- IEC 60947-3

Link to the reference

<https://apac.socomec.com/en/reference/29054013>

SIDER are manually operated 3 or 4-pole load break switches.

They make and break under load conditions and provide safe isolation for any low voltage circuit.

----- System -----

Fill rate E-Order Common	17
Fill rate E-Order Selection	100

Classification

UNSPSC	39122233
ETIM Class	EC000216
IGCC	5290

Commerce

Effective date	1988-12-21
Obsolescence date	2021-07-01
Production ban date	2021-12-31
Country of origin	FR
Discount Policy	1CA40
Discount Policy Label	SIDER

ETIM - Electrical characteristics

Max. rated operation voltage Ue AC [V]	690
Rated operating voltage [V]	400..690
Rated permanent current Iu [A]	125
Rated permanent current at AC-23, 400 V [A]	125
Rated permanent current at AC-21, 400 V [A]	125
Rated operation power at AC-23, 400 V [kW]	63
Switching power at 400 V [kW]	63
Number of poles	4

ETIM - Mechanical characteristics

Suitable for floor mounting	No
Suitable for front mounting 4-hole	Yes
Suitable for front mounting centre	No
Suitable for distribution board installation	No
Suitable for intermediate mounting	Yes
Colour control element	Other
Degree of protection (IP), front side	IP20

ETIM - Technical features

Version as main switch	Yes
Version as maintenance-/service switch	Yes
Version as safety switch	Yes
Version as emergency stop installation	Yes
Version as reversing switch	No
Number of switches	1
Motor drive optional	No
Motor drive integrated	No
Voltage release optional	No
Device construction	Built-in device fixed built-in technique
Type of control element	Other
Interlockable	Yes

Type of electrical connection of main circuit	Bolt connection
Logistics	
GTIN/EAN	3596031143153
Customs number	8536508090
Price unit	PC
Weight of the packing unit	1.727
Length of the packing unit	0.08
Width of the packing unit	0.13
Depth of the packing unit	0.14
Norms	
Conformity to standards	IEC
Technical Characteristics	
Control operator	Direct : F2 / External : S2
Number of poles	4
Rated voltage	690 VAC - 500 VDC
Rated current	125
Type	Lateral operation
Frame size	3