

36556080

Switch-discon-fuse visi break FUSOMAT ST coil-Ext&dir R OP-800A-4P-DIN-Fuse S4



Strong points

- Overload tripping
- High breaking capacity
- Improved safety

General characteristics

- 250 A to 1250 A.
- 3P or 4P available.
- Direct or external handle.
- Auxiliary contact optional.

Compliance with standards

- IEC 60947-3

Link to the reference

<https://apac.socomec.com/en/reference/36556080>

FUSOMAT fuse-combination switches are manually operated 3 or 4-pole load break switches with visible breaking and a remote tripping function.

They provide load operation, safety disconnection and protection against overloads and short-circuits in any low voltage electrical circuit. They can ensure the automatic opening of the circuit together with:

- Fuse blown detection system (see DDMM or FMD)
- Thermal relay
- Differential relay (see RESYS)
- other safety devices

----- System -----

Fill rate E-Order Common	33
Fill rate E-Order Selection	80

Classification

UNSPSC	39122233
ETIM Class	EC001040
IGCC	5291

Commerce

Effective date	2001-01-31
Obsolescence date	2021-07-31
Production ban date	2021-12-31
Country of origin	FR
Discount Policy	1CC60
Discount Policy Label	FUSOMAT_COMBINATION

ETIM - Electrical characteristics

Max. rated operation voltage Ue AC [V]	690
Rated permanent current Iu [A]	800
Number of poles	4

ETIM - Mechanical characteristics

Cable entry	Top/bottom
Equipped with connectors	No
Suitable for floor mounting	Yes
Suitable for front mounting	Yes
Suitable for busbar mounting	No
Degree of protection (IP), front side	IP20

ETIM - Technical features

Version as main switch	Yes
Version as safety switch	Yes
Suitable for fuses	NH4
With error protection	No
Type of electrical connection of main circuit	Bolt connection
Type of control element	Long turning handle
Position control element	Left
Motor drive optional	No
Motor drive integrated	No
Version as emergency stop installation	Yes

Logistics

GTIN/EAN	3596031565740
----------	---------------

Customs number	8536309090
Price unit	PC
Weight of the packing unit	33
Norms	
Conformity to standards	IEC
Technical Characteristics	
Fuse size	NH4
Number of poles	4
Rated current	800
Type	I-O