


36556121

Switch-discon-fuse visi break FUSOMAT ST coil-Ext&dir R OP-1250A-4P-DIN-Fuse S4



Strong points

- Overload tripping
- High breaking capacity
- Improved safety

General characteristics

- 250 A to 1250 A.
- 3P or 4P available.
- Direct or external handle.
- Auxiliary contact optional.

Compliance with standards

- IEC 60947-3

Link to the reference

<https://apac.socomec.com/en/reference/36556121>

FUSOMAT fuse-combination switches are manually operated 3 or 4-pole load break switches with visible breaking and a remote tripping function.

They provide load operation, safety disconnection and protection against overloads and short-circuits in any low voltage electrical circuit. They can ensure the automatic opening of the circuit together with:

- Fuse blown detection system (see DDMM or FMD)
- Thermal relay
- Differential relay (see RESYS)
- other safety devices

Classification

| | |
|------------|----------|
| UNSPSC | 39122233 |
| ETIM Class | EC001040 |
| IGCC | 5291 |

Commerce

| | |
|-------------------|------------|
| Effective date | 1992-01-22 |
| Country of origin | FR |

ETIM - Electrical characteristics

| | |
|---|------|
| Max. rated operation voltage Ue AC [V] | 690 |
| Rated permanent current Iu [A] | 1250 |
| Rated operation power at AC-23, 400 V [kW] | 560 |
| Conditioned rated short-circuit current Iq [kA] | 100 |
| Number of poles | 4 |

ETIM - Mechanical characteristics

| | |
|---------------------------------------|------------|
| Cable entry | Top/bottom |
| Equipped with connectors | No |
| Suitable for floor mounting | Yes |
| Suitable for front mounting | Yes |
| Suitable for busbar mounting | No |
| Degree of protection (IP), front side | IP20 |

ETIM - Technical features

| | |
|---|---------------------|
| Version as main switch | Yes |
| Version as safety switch | Yes |
| Suitable for fuses | NH4 |
| With error protection | No |
| Type of electrical connection of main circuit | Bolt connection |
| Type of control element | Long turning handle |
| Position control element | Left |
| Motor drive optional | No |
| Motor drive integrated | No |
| Version as emergency stop installation | Yes |

Logistics

| | |
|----------------------------|---------------|
| GTIN/EAN | 3596031185962 |
| Customs number | 8536309090 |
| Price unit | PC |
| Weight of the packing unit | 33.78 |

Norms

| | |
|-------------------------|-----|
| Conformity to standards | IEC |
|-------------------------|-----|

Technical Characteristics

| | |
|-----------------|------|
| Fuse size | NH4 |
| Number of poles | 4 |
| Rated current | 1250 |
| Type | I-0 |