

36603041

Switch-discon-fuse visi break FUSOMAT ST coil-Ext&Dir F OP-400A-3P-BS-Fuse B1-B4

Strong points

- Overload tripping
- High breaking capacity
- Improved safety

General characteristics

- 250 A to 1250 A.
- 3P or 4P available.
- Direct or external handle.
- Auxiliary contact optional.

Compliance with standards

- IEC 60947-3

Link to the reference

<https://apac.socomec.com/en/reference/36603041>

FUSOMAT fuse-combination switches are manually operated 3 or 4-pole load break switches with visible breaking and a remote tripping function.

They provide load operation, safety disconnection and protection against overloads and short-circuits in any low voltage electrical circuit. They can ensure the automatic opening of the circuit together with:

- Fuse blown detection system
- thermal relay
- Differential relay
- other safety devices

----- System -----

| | |
|-----------------------------|----|
| Fill rate E-Order Common | 14 |
| Fill rate E-Order Selection | 80 |

Classification

| | |
|------------|----------|
| UNSPSC | 39122233 |
| ETIM Class | EC001040 |
| IGCC | 5291 |

Commerce

| | |
|-----------------------|---------------------|
| Effective date | 1992-02-27 |
| Obsolescence date | 2023-06-30 |
| Production ban date | 2023-12-30 |
| Country of origin | FR |
| Discount Policy | 1CC60 |
| Discount Policy Label | FUSOMAT_COMBINATION |

ETIM - Electrical characteristics

| | |
|--|-----|
| Max. rated operation voltage Ue AC [V] | 690 |
| Rated permanent current Iu [A] | 400 |
| Number of poles | 3 |

ETIM - Mechanical characteristics

| | |
|---------------------------------------|------------|
| Cable entry | Top/bottom |
| Equipped with connectors | No |
| Suitable for floor mounting | Yes |
| Suitable for front mounting | Yes |
| Suitable for busbar mounting | No |
| Degree of protection (IP), front side | IP20 |

ETIM - Technical features

| | |
|---|---------------------|
| Version as main switch | Yes |
| Version as safety switch | Yes |
| Suitable for fuses | Shape B1-B3 |
| With error protection | No |
| Type of electrical connection of main circuit | Bolt connection |
| Type of control element | Long turning handle |
| Position control element | Front side |
| Motor drive optional | No |
| Motor drive integrated | No |
| Version as emergency stop installation | Yes |

Logistics

| | |
|----------|---------------|
| GTIN/EAN | 3596031186150 |
|----------|---------------|

| | |
|----------------------------------|-------------|
| Customs number | 8536309090 |
| Price unit | PC |
| Weight of the packing unit | 10.25 |
| Length of the packing unit | 0.405 |
| Width of the packing unit | 0.265 |
| Depth of the packing unit | 0.31 |
| Norms | |
| Conformity to standards | IEC |
| Technical Characteristics | |
| Fuse size | B1-B2-B3-B4 |
| Number of poles | 3 |
| Rated current | 400 |
| Type | I-0-Test |