


**32153120**

## **Polyester safety enclosure 3P 1250A with top/bottom connection front operation**



### **Strong points**

- Operator safety
- Inductive load breaking (AC23)
- Robust design
- Operating continuity

### **General characteristics**

- Equipped with SIDER load break switches.
- Polyester enclosure.
- Visible breaking.
- Double locking.
- Red handle.
- HB or BB connection.
- The enclosure includes an earthing bar for the connection.
- Protection screen for live parts.

### **Compliance with standards**

- IEC 60947-3
- IEC 61439-2
- IEC 60364
- IEC 60204-1

### **Link to the reference**

<https://apac.socomec.com/en/reference/32153120>

Safety enclosures equipped with SOCOMEC switches provide emergency breaking, breaking for mechanical maintenance, safety isolation and lock out in the vicinity of any low voltage final circuit.

#### ----- System -----

|                             |    |
|-----------------------------|----|
| Fill rate E-Order Common    | 29 |
| Fill rate E-Order Selection | 62 |

#### Classification

|            |          |
|------------|----------|
| UNSPSC     | 39122205 |
| ETIM Class | EC000216 |
| IGCC       | 5176     |

#### Commerce

|                       |                  |
|-----------------------|------------------|
| Effective date        | 2007-05-24       |
| Obsolescence date     | 2023-06-01       |
| Production ban date   | 2023-12-01       |
| Country of origin     | FR               |
| Discount Policy       | 1CN10            |
| Discount Policy Label | STD SAFETY ENCL. |

#### ETIM - Electrical characteristics

|   |          |
|---|----------|
| Max. rated operation voltage Ue AC [V]      | 690      |
| Rated operating voltage [V]                 | 400..690 |
| Rated permanent current Iu [A]              | 1250     |
| Rated permanent current at AC-21, 400 V [A] | 1250     |
| Rated operation power at AC-3, 400 V [kW]   | 1250     |
| Number of poles                             | 3        |

#### ETIM - Mechanical characteristics

|  |      |
|--|------|
| Suitable for floor mounting                  | No   |
| Suitable for front mounting 4-hole           | Yes  |
| Suitable for front mounting centre           | No   |
| Suitable for distribution board installation | No   |
| Suitable for intermediate mounting           | No   |
| Colour control element                       | Red  |
| Degree of protection (IP), front side        | IP55 |

#### ETIM - Technical features

|   |                            |
|---|----------------------------|
| Version as main switch                        | No                         |
| Version as maintenance-/service switch        | Yes                        |
| Version as safety switch                      | Yes                        |
| Version as emergency stop installation        | Yes                        |
| Version as reversing switch                   | No                         |
| Number of switches                            | 1                          |
| Motor drive optional                          | No                         |
| Motor drive integrated                        | No                         |
| Voltage release optional                      | No                         |
| Device construction                           | Complete device in housing |
| Type of control element                       | Door coupling rotary drive |
| Interlockable                                 | Yes                        |
| Type of electrical connection of main circuit | Bolt connection            |

**Logistics**

|                            |               |
|----------------------------|---------------|
| GTIN/EAN                   | 3596031878611 |
| Customs number             | 8536508090    |
| Price unit                 | PC            |
| Weight of the packing unit | 0.01          |

**Technical Characteristics**

|                 |                            |
|-----------------|----------------------------|
| Number of poles | 3                          |
| Rated current   | 1250                       |
| Type            | Polyester safety enclosure |