

**38153010**

## Switch-discon-fuse FUSERBLOC-Dir L OP-100A-3P-NFC-Fuse 22x58

### Strong points

- Improved safety
- High breaking capacity
- Multi-use
- Simplified use

### General characteristics

- For fuses up to 1250 A.
- 2P, 3P or 4P available.
- Up to 690 VAC.
- Up to 100 kA.
- Available in versions with right front-side, left side and central front operation handles.

### Compliance with standards

- IEC 60947-3
- IEC 60269-1
- IEC 60269-2

### Link to the reference

FUSERBLOC NFC/DIN units are manually operated multipolar fuse load break switches.

They provide make and break on load and safety isolation and protection against overcurrent for any low voltage electrical circuit.

This range is available in right front-side, left side and central front, direct or external operation, with 2, 3 and 4 poles and up to 1250 A.

### ----- System -----

Fill rate E-Order Common	17
Fill rate E-Order Selection	100

### Classification

UNSPSC	39122233
ETIM Class	EC001040
IGCC	5291

### Commerce

Effective date	2004-05-04
Country of origin	TN
Discount Policy	1CC24
Discount Policy Label	FUSERBL. MODULAR NFC

### ETIM - Electrical characteristics

Max. rated operation voltage Ue AC [V]	690
Rated permanent current Iu [A]	100
Rated operation power at AC-23, 400 V [kW]	51
Conditioned rated short-circuit current Iq [kA]	100
Number of poles	3

### ETIM - Mechanical characteristics

Cable entry	Top/bottom
Equipped with connectors	No
Suitable for floor mounting	Yes
Suitable for front mounting	Yes
Suitable for busbar mounting	No
Degree of protection (IP), front side	IP20

### ETIM - Technical features

Version as main switch	Yes
Version as safety switch	Yes
Suitable for fuses	22x58 mm
With error protection	No
Type of electrical connection of main circuit	Bolt connection
Type of control element	Rocker lever
Position control element	Left
Motor drive optional	No
Motor drive integrated	No
Version as emergency stop installation	Yes

### Logistics

GTIN/EAN	3596031742578
Customs number	8536303099
Price unit	PC
Weight of the packing unit	1.853

<https://apac.socomec.com/en/reference/38153010>

Length of the packing unit	0.21
Width of the packing unit	0.16
Depth of the packing unit	0.175
<b>Norms</b>	
Conformity to standards	IEC
<b>Technical Characteristics</b>	
Fuse size	22x58
Number of poles	3
Rated current	100
Type	I-0
Frame size	3