

38213063

Switch-discon-fuse FUSERBLOC -Ext&Dir F/L R OP-630A-3P-BS-Fuse C1-C2

Strong points

- Improved safety
- High breaking capacity
- Multi-use
- Simplified use

General characteristics

- For industrial fuses up to 1250 A.
- 2P, 3P or 4P available.
- Up to 690 VAC.
- Up to 100 kA.

Compliance with standards

- IEC 60947-3
- BS EN 60947-3
- IEC 60269-1
- IEC 60269-2

Link to the reference



<https://apac.socomec.com/en/reference/38213063>

FUSERBLOC BS 88 units with right front-side operation are manually-operated multipole fuse load break switches.

They provide make and break on load and safety isolation and protection against overcurrent for any low voltage electrical circuit.

This range is available in direct and external operation, in 2, 3 and 4 poles and up to 1250 A.

Classification

UNSPSC	39122233
ETIM Class	EC001040
IGCC	5291

Commerce

Effective date	2003-03-03
Country of origin	FR
Discount Policy	1CC45
Discount Policy Label	FUSER MOD. BS >400
Length of the product unit	0.3
Width of the product unit	0.364
Depth of the product unit	0.25
Weight	18.67

ETIM

Version as main switch	Yes
Version as safety switch	Yes
Max. rated operation voltage Ue AC [V]	690
Rated permanent current Iu [A]	630
Rated operation power at AC-23, 400 V [kW]	355
Conditioned rated short-circuit current Iq [kA]	100
Suitable for fuses	Shape C1-C3
Number of poles	3
With error protection	No
Type of electrical connection of main circuit	Bolt connection
Cable entry	Top/bottom
Equipped with connectors	No
Suitable for floor mounting	Yes
Suitable for front mounting	Yes
Suitable for busbar mounting	No
Type of control element	Long turning handle
Position control element	Front side
Motor drive optional	No
Motor drive integrated	No
Version as emergency stop installation	Yes
Degree of protection (IP), front side	IP20

Logistics

GTIN/EAN	3596031659265
Customs number	8536309090
Price unit	PC
Weight of the packing unit	18.67
Length of the packing unit	0.44
Width of the packing unit	0.4

Depth of the packing unit	0.52
Norms	
Conformity to standards	IEC
Technical Characteristics	
Control operator	Direct : H1 / External : S3
Fuse size	C1-C2
Number of poles	3
Rated current	630
Type	I-0
Frame size	17