

38312015

Switch-discon-fuse FUSERBLOC-Ext&Dir F/L R OP-160A-2P-DIN-Fuse S00

Strong points

- Improved safety
- High breaking capacity
- Multi-use
- Specific functionalities for simplified use

General characteristics

- 25 to 1250 A.
- Up to 690 VAC.
- Up to 100 kA.
- Available in 2P, 3P or 4P, from 25 to 1250 A.

Compliance with standards

- IEC 60947-3
- IEC 60269-1
- IEC 60269-2

Link to the reference



<https://apac.socomec.com/en/reference/38312015>

Front/side control FUSERBLOCs are manually operated multipolar fuse load break switches.

They make and break on load and provide safety isolation and protection against overcurrent for any low voltage electrical circuit.

This range includes both direct and external-control models, with 2, 3 and 4 poles and from 25 to 1250 A.

Classification

UNSPSC	39122233
ETIM Class	EC001040
IGCC	5291

Commerce

Effective date	2001-11-13
Country of origin	FR
Discount Policy	1CC34
Discount Policy Label	FUSER MODULAR DIN
Length of the product unit	0.162
Depth of the product unit	0.1265
Weight	1.41

ETIM

Cable entry	Top/bottom
Suitable for fuses	NH00
Suitable for front mounting	Yes
Suitable for busbar mounting	No
With error protection	No
Position control element	Front side
Equipped with connectors	No

ETIM - Electrical characteristics

Rated permanent current Iu	160
Number of poles	2
Conditioned rated short-circuit current Iq	100
Rated operation power at AC-23, 400 V	51
Max. rated operation voltage Ue AC	690

ETIM - Mechanical characteristics

Degree of protection (IP), front side	IP20
Suitable for floor mounting	Yes

ETIM - Technical features

Motor drive integrated	No
Type of electrical connection of main circuit	Bolt connection
Version as emergency stop installation	Yes
Type of control element	Long turning handle
Version as main switch	Yes
Version as safety switch	Yes
Motor drive optional	No

Logistics

GTIN/EAN	3596031601295
Customs number	8536309090
Price unit	PC

Weight of the packing unit	1.41
Length of the packing unit	0.155
Width of the packing unit	0.17
Depth of the packing unit	0.21
Norms	
Conformity to standards	IEC UL
Technical Characteristics	
Control operator	Direct : H11 / External : S2
Fuse size	NH0
Number of poles	2
Rated current	160
Type	I-0-Test
Frame size	13